






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
1	-		A	FIRST ISSUE	12FEB2009	AV	GT
			C	UPDATED PART REVISION	24FEB2011	AV	GT



SECTION X - X



- NOTES:
- SUITABLE FOR SOCKET CONTACT 293389
 - CONTACT ACCEPTS WIRE SIZE 18 AWG
 - SEMI-AUTOMATIC TOOL AND HAND TOOL (EACH FOR 2 CRIMPS IN ONE CYCLE) TO BE DEVELOPED
 - STRIPPED CABLE LENGHT FOR CRIMP IS 3.5mm
 - WEIGHT ABOUT 0.12g
 - DIE FEED 7.0mm
 - REELED ON PAPER-REEL



DIRECTION OFF TOP OF REEL

Fertig-zustand

8

107-3(Fig.1)

8	NOT AVAILABLE	293390-1	C	2	SPRING	A	STEEL	
				1	BODY	B	CuNiSi AMP-Spec. 100-1230 or 112-18011	TIN PLATED
DIRECTION OFF TOP OF REEL	LOOSE PIECE	PART NO	REV	POS	DESCRIPTION	REV	MATERIAL	FINISH
THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.					DWN 12FEB2009 CHK A. Vecchia G. Turco APVD 12FEB2009 G. Turco	Tyco Electronics AMP Italia S.r.l. 10093 Collegno TO		
DIMENSIONS: mm					PRODUCT SPEC 108-20294	MICRO QUADLOK SYSTEM SOCKET CONTACT		
TOLERANCES UNLESS OTHERWISE SPECIFIED:					APPLICATION SPEC 114-20140			
MATERIAL					WEIGHT 0.12g	SIZE A2	CAGE CODE 00779	DRAWING NO C-293390
SEE TABLE					CUSTOMER DRAWING	SCALE 10:1	SHEET 1	OF 1
								REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[293390-1](#)