




REVISIONS


| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|-----------------|-----------|-----|------|
| | C2 | REVISED DRAWING | 13FEB2019 | RSM | MZ |



KEYING POLARIZATION FOR
P/N 293408-1 (WHITE VERSION)
AND FOR
P/N 293408-2 (BLACK VERSION)



KEYING POLARIZATION FOR
P/N 293408-3 (GRAY VERSION)



1 PACKAGING: N° 1500 PCS INTO CARTON BOX, ACCORDING TO TE SPEC. 107-20297

2 Ø7.70 INCLUDING THE MARKS & WRITINGS

THE PRESENTED PRODUCT / DESIGN WILL BE
RELEASED FOR THE MANUFACTURING OF
THE NECESSARY PRODUCTION TOOLS HEREBY.
FURTHER CHANGES HAS TO BE PAYED BY CUSTOMER.

DATE, SIGN OF THE CUSTOMER

| | | |
|--------|-------------|------|
| GRAY | 293408-3 | B |
| BLACK | 293408-2 | B |
| WHITE | 293408-1 | B |
| COLOUR | PART NUMBER | REV. |



RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT - TE Connectivity Ltd.



| | | | | | | | | | | |
|--|--|----------------------------------|---|-----------|-------------|----------|--|--------|-----|----|
| DIMENSIONS: mm | | DWN D. CHIARELLI 22JUN2009 | MATERIAL PA, ACC.TO GLOW WIRE 750°C NO FLAME | | FINISH — | | | | | |
| | | CHK D. CHIARELLI 22JUN2009 | <div>TE Connectivity Ltd.</div> | | | | | | | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: | | APVD G. TURCO 22JUN2009 | | | | | NAME 4 POS. LOW VOLTAGE, FREE HANGING FEMALE CONN. HOUSING FOR EUROPE MARKET | | | |
| | | PRODUCT SPEC — | | | | | | | | |
| | | APPLICATION SPEC — | SIZE | CAGE CODE | DRAWING NO | | RESTRICTED TO — | | | |
| | | WEIGHT — | A4 | | 00779 | C-293408 | | | | |
|  | | CUSTOMER DRAWING | | | SCALE | 2:1 | SHEET | 1 OF 1 | REV | C2 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[293408-1](#)