

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT -- By -- ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D2	REVISED PER ECO-11-010839	25MAY11	RK	HMR
	D3	REVISED PER ECO-18-002614	28FEB2018	RS	DR
	D4	REVISED PER ECO-19-015407	22OCT2019	RS	DR

AMP
WIRE RANGE

26-22 AWG
STRANDED



- 1

STAMP AMP APPROX AS SHOWN
- 2

CLEANED, UNPLATED
- 3

TIN PLATE 0.00254[.000100]
MIN EXT THK PER ASTM B545

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170° C[338°F] MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 0.1-0.41mm ² [202-810] CIR MILS STRANDED
FOR ORDER ENTRY	1-800-526-5142	

5000	TAPE & REEL	3	31428-2
1000	LOOSE PIECE	2	31428-1
1000	LOOSE PIECE	3	31428
QTY	PACKAGE TYPE	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 2-2-93	TE TE Connectivity Ltd.	
		CHK DA PATTERSON 2-2-93		
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD DE MILLER 2-2-93	NAME	
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ASTM B-152 ANNEALED ANGLES ± -	PRODUCT SPEC	TERMINAL, RING TONGUE, BUDGET 26-22 AWG	
		APPLICATION SPEC	SIZE	RESTRICTED TO
MATERIAL COPPER PER ASTM B-152 ANNEALED	FINISH -3	WEIGHT	CAGE CODE 00779	DRAWING NO C=31428
CUSTOMER DRAWING			SCALE 10:1	SHEET 1 OF 1
			REV D4	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[31428](#)