



LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
GP	00		C1	REVISE PER ECO-09-001401	26JAN09	DH	DY	
			C2	REVISED PER ECO-09-024717	06NOV09	KK	AEG	

D





SEE TABLE FOR
OF ROWS



A B C D E


PIN PATTERN

C




- 1 HOUSING MATERIAL: POLYESTER PBT,MOLDING COMPOUND, FLM RTD, 20% GLASS FILLED, COLOR:BLACK.
- 2 CONTACT MATERIAL: PHOSPHOR BRONZE PER UNS C51100, TEMPER H04
- 3 CONTACT FINISH:
MATING SURFACE- 0.0008 MIN GOLD OVER 0.0013 MIN NICKEL.
ON LEADS- 0.0005 MIN TIN-LEAD OVER 0.0013 MIN NICKEL.
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

B



0.6±0.05 DIA
PLATED THROUGH HOLE
CC PLC



RECOMMENDED PCB
PATTERN

4	OBSOLETE	175	48	49.88	25	-2-319919-2-
	OBSOLETE	168	46	47.88	24	-2-319919-1-
		161	44	45.88	23	-2-319919-0-
4	OBSOLETE	154	42	43.88	22	-1-319919-9-
	OBSOLETE	147	40	41.88	21	-1-319919-8-
		140	38	39.88	20	-1-319919-7-
4	OBSOLETE	133	36	37.88	19	-1-319919-6-
		126	34	35.88	18	-1-319919-5-
		119	32	33.88	17	-1-319919-4-
		112	30	31.88	16	-1-319919-3-
	OBSOLETE	105	28	29.88	15	-1-319919-2-
		98	26	27.88	14	-1-319919-1-
		91	24	25.88	13	-1-319919-0-
		84	22	23.88	12	-319919-9-
4	OBSOLETE	77	20	21.88	11	-319919-8-
	OBSOLETE	70	18	19.88	10	-319919-7-
		63	16	17.88	9	-319919-6-
		56	14	15.88	8	319919-5
4	OBSOLETE	49	12	13.88	7	-319919-4-
		42	10	11.88	6	319919-3
		35	8	9.88	5	319919-2
		28	6	7.88	4	319919-1
		CC	BB	AA	ROWS	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SMITH CHK C.ADAMS APVD T.SMITH PRODUCT SPEC	220CT97	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APPLICATION SPEC	NAME	SIZE	RESTRICTED TO
	0 PLC ± 0.1 1 PLC ± 0.1 2 PLC ± 0.1 3 PLC ± 0.1 4 PLC ± 0.1 ANGLES ± 0.1	—	—	—	—
MATERIAL	FINISH	WEIGHT	—	—	—
—	—	—	—	—	—
CUSTOMER DRAWING		SCALE	5:1	SHEET	1 OF 1
		REV	C2		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[319919-1](#)