






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	REDRAWN PER ECR 09-016745	28JUL09	JR	TM
	B2	REVISED PER ECO-17-007400	27NOV2017	RS	DR



AMP WIRE RANGE	FILE E13288
12-10 AWG STRANDED	12-10 AWG STRANDED

- 1 WIRE INSUL ϕ 3.810-5.842[ϕ .150-.230]
- 2 MATERIAL: BODY - CU PER ASTM B152
SLEEVE - CU PER ASTM B152
INSULATION - NYLON ASTM D4066 TYPE 1.
- 3 FINISH: BODY & SLEEVE: TIN PER ASTM B-545
INSULATION - COLOR: YELLOW.
- 4 STAMP AMP 12-10* 6-9 APPROX AS SHOWN.

500	LOOSE PIECE	320620
QTY	PACKAGE TYPE	PART NO

MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr_ruth 12JUN09		<div>TE Connectivity</div>				
			CHK TOM MICHIELUTTI 12JUN09						
VOLTAGE RATING: 300 V MAX	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± 5°		APVD TOM MICHIELUTTI 12JUN09	NAME TERMINAL, PIDG, KNIFE DISCONNECT, WIRE SIZE: 12-10				
				PRODUCT SPEC UL 486A-B					
CIRCULAR MIL AREA: 2.62-6.64mm² [5,180-13,100] STRANDED		FINISH 		APPLICATION SPEC 114-2157	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO —	
				WEIGHT —	A3	00779	C=320620		
				CUSTOMER DRAWING					SCALE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[320620](#)