




LOC		DIST		REV		DATE		APD	
G	14	P	F	ZONE	LTR	DESCRIPTION	DATE	APD	18 DAP
				F	REV, RDRW, & SM	PKG PER 0720-0040-93	4-8-93		



AMP WIRE RANGE		UL E13288 Listed	
22-16 AWG	SOLID OR STRANDED	22-16 AWG	SOLID OR STRANDED
LR7189 Certified		MILITARY P/N AND CLASS	
22-16 AWG SOLID OR STRANDED		NOT APPLICABLE	

△ STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPECIFICATION
MIL-T-7928, COMMERCIAL WIRE RANGE IS 22-16



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 0.26-1.65mm² [509-3,260] CIR MILS SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLG DEC ± 3 PLG DEC ±	ANGLES ± -	FINISH TIN PLATE 0.00254 [1.000100] MIN THK PER MIL-T-10727
--	------------------	--

DR 4-8-93 TA BRINKMAN	CHK 4-8-93 DA PATTERSON	NAME
APPD 4-8-93 DE MILLER	APPD 4-8-93 JL MECKLEY	PRODUCT SPEC
		APPLICATION SPEC
		WEIGHT

100	LOOSE PIECE BOX	8-320749-1
5000	ON TAPE	2-320749-2
----	LOOSE PIECE	320749
QUANTITY	PACKAGE TYPE	PART NO

AMP
AMP Incorporated
Harrisburg, PA 17105-3608

TERMINAL, FLANGED
SPADE, SOLISTRAND™

SIZE	CAGE CODE	DRAWING NO
③	00779	③=320749
SCALE 10:1		SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-320749-2](#)