



LOC		DIST		P		F		ZONE		LTR		REVISIONS		DATE		APPD	
G		14								C		REV & REDRAWN PER 0720-0040-93		3-26-93		1AP DAP	

METRIC

DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	 E13288 Listed
12-10 AWG SOLID OR STRANDED	12-10 AWG STRANDED
 LR7189 Certified	MILITARY P/N AND CLASS
12-10 AWG SOLID OR STRANDED	NOT APPLICABLE

1 STAMP AMP 12-10* APPROX AS SHOWN



					2500	ON TAPE		2-321499-1	
					----	LOOSE PIECE		321499	
					QUANTITY	PACKAGING TYPE		PART NO	
AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX	DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± - MATERIAL COPPER PER ASTM B-152 ANNEALED FINISH TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727	DR 3-26-93 TA BRINKMAN		AMP AMP Incorporated Harrisburg, PA 17105-3608			
		CHK 3-26-93 DA PATTERSON							
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		VOLTAGE RATING: NOT APPLICABLE		APPD 3-26-93 DE MILLER		NAME TERMINAL, RECTANGULAR TONGUE, SOLISTRAND™			
PRODUCT INFORMATION CENTER 1-800-522-6752				APPD 3-26-93 JL MECKLEY					
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 2.62-6.64mm² [5,180-13,100] CIR MILS SOLID OR STRANDED	PRODUCT SPEC -					
FOR ORDER ENTRY		1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	APPLICATION SPEC -		SIZE C	CAGE CODE 00779	DRAWING NO C=321499	
				WEIGHT -		SCALE 10:1		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-321499-1](#)