

LOC —	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			G1	NEW DRAWING PER ECO-11-019045	03APR12	KH	DR



MATERIAL: BRASS PER ASTM-B19 0.812[.032] THK.
INSULATION: PVC






FINISH : TIN PLATE PER ASTM-B545

3 FOR WIRE SIZE 22-10

4 CSA LISTED LR7189, UL RECOGNIZED E66717

5 105°C[221°F] MAX TEMPERATURE.

6 600V MAX VOLTAGE.



321688

PART NO

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT - By -

DIMENSIONS: mm [INCHES]		DWN KIRAN HOLAL 03APR12	MATERIAL 	FINISH
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK ROHDE DANIEL 03APR12	TE Connectivity	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD ROHDE DANIEL 03APR12		
PRODUCT SPEC —		NAME FASTON SPLICE 250 SERIES		
APPLICATION SPEC —		SIZE A4	CAGE CODE 00779	DRAWING NO C-321688
WEIGHT —		RESTRICTED TO —		
		CUSTOMER DRAWING		
SCALE 4:1		SHEET 1 OF 1		REV G1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[321688](#)