


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G3	REVISED PER ECO-17-004099	24AUG2017	BDA	DR
	G4	REVISED PER ECO-18-010020	26JUN2018	RS	DR






AMP WIRE RANGE	E13288 Listed
1/0 AWG SOLID OR STRANDED	1/0 AWG STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
1/0 AWG SOLID OR STRANDED	MS 20659-118 CLASS 2

TIN PL 0.00254[.000100] MIN EXT. THK
PER ASTM B-545

2 NOTE DELETED

	50	LOOSE PIECE	CLEANED	COPPER ASTM B-152 1.778±0.076[.070±.003] ANNEALED	2-321868-2
	50	LOOSE PIECE			321868
	QTY.	PACKAGE TYPE	FINISH	MATERIAL	PART NUMBER

MAX RECOMMENDED OPERATING TEMPERATURE: 170°[338°F]C	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 8/30/91	<div>TE Connectivity Ltd.</div>			
			CHK RD HEIM 9/30/91				
VOLTAGE RATING: N/A	DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED: <div><div>0 PLC ± -</div><div>1 PLC ± -</div><div>2 PLC ± -</div><div>3 PLC ± 0.127[.005]</div><div>4 PLC ± -</div><div>ANGLES ± -</div></div>	APVD AJ KAUFMAN 9/30/91	NAME TERMINAL, RING TONGUE, SOLISTRAND WIRE SIZE 50.0mm2 [1/0] AWG			
			PRODUCT SPEC UL 486 A-B				
CIRCULAR MIL AREA: 42.4-60.6mm² [83,700-119,500] SOILD OR STRANDED		TOLERANCES UNLESS OTHERWISE SPECIFIED: <div><div>0 PLC ± -</div><div>1 PLC ± -</div><div>2 PLC ± -</div><div>3 PLC ± 0.127[.005]</div><div>4 PLC ± -</div><div>ANGLES ± -</div></div>	APPLICATION SPEC —	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
			WEIGHT —	A3	00779	C-321868	—
			MATERIAL SEE TABLE	FINISH SEE TABLE	CUSTOMER DRAWING		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[321868](#)