

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD


G

REV / 0720-0660-95

07JUL95

ME

SB



1 STAMP AMP 16-14*APPROX AS SHOWN


2. WIRE INSUL DIA, 3.05-4.32 [0.120-0.170]

3. TONGUE MATL THK, 0.79±0.05 [0.031±0.002]

4 NICKEL PLATE PER QQ-N-290

5 GOLD PLATE PER MIL-G-45204 OVER
NICKEL PLATE PER QQ-N-290

1000	LOOSE PIECE	322274-1
1000	LOOSE PIECE	322374
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMMAX RECOMMENDED OPERATING
TEMPERATURE:
343°C [650°F]THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.DIMENSIONS:
mm [in]TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ±-
1 PLC ±-
2 PLC ±0.20 [0.008]
3 PLC ±-
4 PLC ±-
ANGLES ±-MATERIAL
BODY, CU PER ASTM B152
SLEEVE, NI SIL PER
ASTM B122FINISH
SEE NOTES 4 & 5

DWN L OLMEDA 100CT94

CHK M ELLIS 100CT94

APVD S BORTNER 100CT94

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

AMP Incorporated
Harrisburg, PA 17105-3608NAME TERMINAL, RING TONGUE,
STRATO-THERM™, DIAMOND GRIP™
WIRE SIZE, 16-14 AWG

SIZE A3 CAGE CODE 00779 DRAWING NO C-322374

SCALE 6:1 SHEET 1 OF 1 REV G

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[322374](#)