

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD

F


REDRAWN PER 0720-0377-94

25OCT94

LO

ME

△ STAMP AMP 16-14*APPROX AS SHOWN



2. WIRE INSUL DIA, 3.05-4.32 [.120-.170]

3. TONGUE MATL THK, 0.79±0.05 [.031±.002]

1000	LOOSE PIECE	322825
QTY	PACKAGE TYPE	PART NO


AMP INCORPORATED
CUSTOMER SERVICE SYSTEM

MAX RECOMMENDED OPERATING
TEMPERATURE:
343°C [650°F]

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm [in]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:



0 PLC ±-
1 PLC ±-
2 PLC ±0.20 [.008]
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL
BODY, CU PER ASTM B152
SLEEVE, NI SIL PER
ASTM B122

FINISH
BODY, NP, QQ-N-290

DWN	L OLMEDA	25OCT94
CHK	M ELLIS	25OCT94
APVD	S BORTNER	25OCT94
PRODUCT SPEC		
APPLICATION SPEC		
WEIGHT	-	
CUSTOMER DRAWING		

AMP AMP Incorporated
Harrisburg, PA 17105-3608

NAME WIRE SPLICE, STRATOTHERM
DIAMOND GRIP, WIRE SIZE,
16-14 AWG

SIZE A3 CAGE CODE 00779 DRAWING NO C-322825

SCALE 6:1 SHEET 1 OF 1 REV F

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

VOLTAGE RATING:
-

CIRCULAR MIL AREA:
1.04mm²-2.62mm² [2050-5180]

STRANDED WIRE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[322825](#)