



LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	DWN
			F1	REV PER ECR 09-027810	29DEC09	JR
						APVD
						TM



AMP
WIRE RANGE



8 AWG
SOLID OR STRANDED

- 1 STAMP AMP 8* APPROX AS SHOWN
- 2 COPPER PER ASTM B-152, ANNEALED
- 3 NICKEL PLATE 0.00762 [$.000300$] MIN THK PER QQ-N-290



323168

PART NO.

MAX RECOMMENDED OPERATING TEMPERATURE: 343°C MAX	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 4-19-93	 Tyco Electronics Corporation Harrisburg, PA 17105-3608			
			CHK DA PATTERSON 4-19-93				
VOLTAGE RATING: N/A	DIMENSIONS: MM [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD JL MECKLEY 4-19-93	NAME TERMINAL, RING TONGUE, HEAT RESISTANT, STRATO-THERM			
			PRODUCT SPEC —				
CIRCULAR MIL AREA: 6.64-10.5mm² [13,100-20,800] SOLID OR STRANDED		FINISH 	APPLICATION SPEC —	SIZE A2	CAGE CODE 00779	DRAWING NO C-323168	RESTRICTED TO —
			WEIGHT —				
			CUSTOMER DRAWING				SCALE 4:1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[323168](#)