

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		F1	REVISED PER ECR-09-021767	05OCT09	JR	TM




FIGURE 1
FOR .080 TO .125 WIRE INSULATION DIA




FIGURE 2
INSULATION RESTRICTING
FOR .056 TO .110 WIRE INSULATION DIA

1 TONGUE MATERIAL THK IS .031±.002

OBSOLETE	1	WIRE TERMINAL INSULATION RESTRICTING	BODY & SLEEVE: COPPER (ASTM-B152) TIN PL (ASTM-B545) INSULATION: NYLON COLOR: RED (ASTM-D4066) TYPE 1	2-324158-2
	5000	324158 ON TAPE	BODY & SLEEVE: COPPER (ASTM-B152) TIN PL (ASTM-B545)	2-324158-1
	1	WIRE TERMINAL	INSULATION: NYLON COLOR: RED (ASTM-D4066) TYPE 1	324158
	QTY	DESCRIPTION	MATERIAL & FINISH	PART NO

2-324158-2	FIGURE 2	#18		OBSOLETE
324158	FIGURE 1	#22-#16	2-324158-1	
PART NO.	STYLE	WIRE SIZE	PART NO. ON TAPE	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 02OCT09		 Tyco Electronics Corporation Harrisburg, PA 17105-3608						
DIMENSIONS: INCHES		CHK TOM MICHELUTTI 02OCT09								
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD MIKE PERCHERKE 02OCT09		NAME TERMINAL, NYLON – PIDG – RING TONGUE WIRE SIZE: 22-16 —					
	0 PLC ± –		PRODUCT SPEC							
	1 PLC ± –		—							
	2 PLC ± –		APPLICATION SPEC							
MATERIAL SEE TABLE	3 PLC ± .008		—		SIZE A2	CAGE CODE 00779	DRAWING NO C-324158	RESTRICTED TO —		
	4 PLC ± –		—							
	ANGLES ± 5°		—							
	FINISH		WEIGHT —							
SEE TABLE		SEE TABLE		CUSTOMER DRAWING				SCALE 10:1	SHEET 1 of 1	REV F1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[324158](#)