



LOC	DIST	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
G	86				U	REV PER 0G3A-0561-01	090CT02	JR/MS



1 CIRCULAR MIL AREA RANGE: 325-375 MCM
2 TIN PL 0.00381 [0.000150] MIN THK PER MIL-T-10727



DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON :
2 PLC DEC ± 0.51 [.020]
3 PLC DEC ± -
ANGLES ± -

MATERIAL
ANNEALED COPPER
ASTM B-75

FINISH



DR 02/28/90
DK SCHRUM

CHK 23JAN95
MS FEHER

APPD 23JAN95
WJ VOCKROTH

APPD 23JAN95
TL SHUTTER

PRODUCT SPEC
108-30200

APPLICATION SPEC
-

WEIGHT .259 LB

NONE

326806-1

REQUIRED

326806

SIGHT HOLE

PART NO



AMP INCORPORATED
Harrisburg, Pa. 17105

NAME

TERMINAL, AMPPOWER™
WIRE SIZE: 350 MCM

SIZE



CAGE CODE
00779

DRAWING NO

326806

SCALE

2:1

SHEET

1 OF 1

METRIC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[326806](#)