



| LOC | DIST | P | F | REVISIONS |     |                      |         |       |
|-----|------|---|---|-----------|-----|----------------------|---------|-------|
|     |      |   |   | ZONE      | LTR | DESCRIPTION          | DATE    | APPD  |
| G   | 86   |   |   |           | E   | REV PER 0G3A-0561-01 | 090CT02 | JR/MS |



- 1 CIRCULAR MIL RANGE: 750-850 MCM
- 2 TIN PL 0.00381 [.000150] MIN THK PER ASTM B 545
- 3 UNPLATED

|                                                                                                                                          |  |                                               |                   |
|------------------------------------------------------------------------------------------------------------------------------------------|--|-----------------------------------------------|-------------------|
|                                                                                                                                          |  | 327292-4                                      |                   |
|                                                                                                                                          |  | 327292                                        |                   |
| FINISH                                                                                                                                   |  | PART NO                                       |                   |
| DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON :<br>2 PLC DEC ± 0.51 [.020]<br>3 PLC DEC ± -<br>ANGLES ± - |  | AMP AMP INCORPORATED<br>Harrisburg, Pa. 17105 |                   |
| MATERIAL                                                                                                                                 |  | NAME                                          |                   |
| ANNEALED COPPER<br>ASTM B-75                                                                                                             |  | TERMINAL, AMPPOWER™                           |                   |
| FINISH                                                                                                                                   |  | WIRE SIZE: 800 MCM                            |                   |
| SEE NOTES                                                                                                                                |  | SIZE                                          | CAGE CODE         |
|                                                                                                                                          |  | C                                             | 00779             |
| WEIGHT .821 LB                                                                                                                           |  | SCALE 1:1                                     | DRAWING NO 327292 |
|                                                                                                                                          |  |                                               | SHEET 1 OF 1      |



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[327292-4](#)