



LOC	DIST	REVISIONS				DAP		
		P	LTR	DESCRIPTION		DATE	OWN	APVD
G	14		E2	REVISED PER ECO-11-004820		11MAR11	RK	HMR

WIRE RANGE	Listed FILE E13288	LR7189 Certified
12-10 AWG SOLID OR STRANDED	12-10 AWG STRANDED	12-10 AWG SOLID OR STRANDED



- 1 STAMP AMP 12-10* APPROX AS SHOWN
- 2 COPPER PER ASTM B-152, ANNEALED
- 3 TIN PLATE 0.00254 [.000100] MIN THK PER ASTM B545
- 4 TIN/LEAD (93-7) PLATE PER ASTM B545 (3% MIN LEAD CONTENT).

25	3	LOOSE PIECE, BAG	8-32994-5
50	3	LOOSE PIECE, BOX	8-32994-2
2500	3	ON TAPE	2-32994-1
500	4	LOOSE PIECE	32994-1
500	3	LOOSE PIECE	32994
QUANTITY	FINISH	PACKAGING TYPE	PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 2.62-6.64mm² [5,180-13,100] SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-17-93	TE Connectivity	
		CHK DA PATTERSON 3-17-93		
DIMENSIONS: MM [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD JL MECKLEY 3-17-93	NAME TERMINAL, RING TONGUE, SOLISTRAND	
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± ± -	PRODUCT SPEC — APPLICATION SPEC —	SIZE A2	CAGE CODE 00779
MATERIAL 	FINISH SEE NOTES	WEIGHT —	DRAWING NO G-32994	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 10:1	SHEET 1 of 1
			REV E2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[32994](#)