

4

3

2

1

© -TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	P2	REVISED PER ECR-20-013876	29SEP2020	ED	RS

1

2

3

1

2

3

4. SEE 408-1771

5. PARTS ARE PACKAGED UNASSEMBLED

6.99 MAX DIA
[.275]

22.61 MAX
[.890]

7.14±0.41
[.281±.016]

5.56±0.41
[.219±.016]

12.70 REF
[.500]

RECOMMENDED STRIP LENGTH

2	69188-1	1-329067-1	1-328695-3	330350-2	2-330311-7	
3	58500-1 & 91911-2	1-329038-3	1-328695-3	330350-2	2-330311-6	
3	58500-1 & 91911-2	329038	1-328695-2	330350	2-330311-4	
2	69188-1	329067	1-328695-2	330350-1	2-330311-3	
2	69188-1	329067	328695	330350	2-330311-2	
1	58500-1 & 91911-2	2087963-2	328695	330350	2-330311-1	
FOR USE WITH CABLE		CRIMPING TOOL	3 FERRULE QTY=1	2 RETAINING COLLAR QTY=1	1 PLUG ASSY QTY=1	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

MATERIAL -

FINISH -

DWN J.DAVIS 01/26/93

CHK G.MICHAEL 01/29/93

APVD G.MICHAEL 1-29-93

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT 0.000000

01/26/93

01/29/93

1-29-93

CONN,COAX,RF
PLUG,MIN THD'D

SIZE A3

CAGE CODE 00779

DRAWING NO C-330311

CUSTOMER DRAWING

SCALE 4:1

SHEET 1 OF 1

REV P2

TE

TE Connectivity

1470-19 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-330311-2](#)