




LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			G	REVISED PER ECO-12-009966	30MAY2012	CJV	SLB

[illegible]

	1-338309-2	—
	2-338309-2	
	3-338309-2	
	4-338309-2	
	5-338309-2	
	6-338309-2	
	7-338309-2	
OBSOLETE	8-338309-2	
OBSOLETE	9-338309-2	



-  GROOVE INDICATES VERSION WITH 4-40 UNC INNER THREAD;
WITHOUT GROOVE INDICATES VERSION WITH M3 INNER
THREAD.

- 2 CAVITY IDENTIFICATION AT FRONT SIDE ONLY.


- PART NUMBER AND DATE CODE.

4. WHEN BOARDLOCKS ARE USED, CONNECTOR CAN BE USED FOR PCB THICKNESS OF 1.6 mm ONLY.

5. SHELL HAS 2x2 GROUNDING SPRINGS; PITCH IS 3.6 mm.

6. AIR AND CREEPAGE DISTANCES ACCORDING TO DIN 41652.

7. CONTACT FINISH: GOLD FLASH OVER PALLADIUM-NICKEL PLATE OR GOLD PLATE ON THE MATING SURFACES, TIN PLATE ON THE SOLDER TAILS, NICKEL UNDERPLATE ON THE ENTIRE CONTACT. MATING SURFACE FINISH MEETS LEVEL 2 PER DIN 41652.



THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009		DWN J.V. LIEMPT 03JUL97		 TE Connectivity	
		CHK C. SOUISA 09SEP97			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME HDP-20 SIZE 1 VERTICAL+ PLUG HEADER; WITH SOLDER CONTACTS	
		APVD F. LEITENS 09SEP97			
		PRODUCT SPEC —			
		APPLICATION SPEC —			
MATERIAL —		FINISH —		SIZE A2	
		WEIGHT —		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-338309	
				RESTRICTED TO —	
				SCALE NTS	
				SHEET 1 of 1	
				REV G	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-338309-2](#)