








LOC	DIST	REVISIONS									
CM	0	P	LTR	DESCRIPTION			DATE	DWN	APVD		
			AP3	REVISED	PER	REVISED	PER	ECR-18-015418	13DEC2018	WH	DZ




- 1 0.000762 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA OVER 0.00127 [.000050] MIN NICKEL.
- 2 WIRE RANGE: 0.3 – 0.84mm² (24–18 AWG).
- 3 INSULATION RANGE: 2.79 [.110] MAX. DIA.
- 4 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 5 0.00127 [.000050] MIN NICKEL



METRIC

5	0.25 [.010] PH BRZ	350417-8
GOLD STRIPE	0.25 [.010] BRASS	350417-5
1	0.25 [.010] BRASS	350417-3
PRE-TIN	0.25 [.010] BRASS	350417-1
FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 22NOV2005	 TE Connectivity						
		CHK D. COLEY 22NOV2005							
DIMENSIONS: mm [INCHES] 	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLC ± - 1. PLC ± - 2. PLC ± - 3. PLC ± 0.13 [.005] 4. PLC ± - ± 0°30' ANGLES	APVD D. COLEY 22NOV2005 PRODUCT SPEC 114-49000 APPLICATION SPEC 114-49000 WEIGHT -	NAME	.093 SOCKET					
			COMMERCIAL PIN AND SOCKET						
			-						
			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
			A1	00779	C=350417	-			
			MATERIAL SEE TABLE		FINISH SEE TABLE		CUSTOMER DRAWING		
				SCALE	N/A	SHEET	1 OF 1	REV	AP3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[350417-1](#)