



- 1
- PLATED WITH .000030 GOLD, OVER .000050 NICKEL UNDERPLATE.
- 2
- GOLD OVER NICKEL ON ENTIRE STAMPING; .000030 GOLD MINIMUM AT POINT OF MEASUREMENT IN CONTACT AREA, GOLD FLASH MINIMUM IN WIRE BARREL.
- 3
- INSULATION RANGE :  $\phi$ .130-.200

350707-7	.012 BRASS	GOLD 1	350700-7
-	.012 PH BR2	PRE-TIN	350700-3
350707-2	.012 BRASS	GOLD 2	350700-2
350707-1		PRE-TIN	350700-1
LOOSE PIECE (REF)	MATERIAL	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0. PLC	± .01
1. PLC	± .01
2. PLC	± .01
3. PLC	± .015
4. PLC	± .01
ANGLES	± .01

MATERIAL: -

FINISH: -

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN: PASVESH, WARAD 31MAR2016

CHK: WICKES, EVAN 31MAR2016

APVD: WICKES, EVAN 31MAR2016

NAME: -

PRODUCT SPEC: 108-1031

APPLICATION SPEC: 114-1010

WEIGHT: 0

CUSTOMER DRAWING

SCALE: 10:1

SHEET: 1 OF 2

REV: Y3

RESTRICTED TO: -

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[350700-3](#)