







CONTACT DIMENSIONS



RECOMMENDED PCB-HOLE LAY-OUT
COMPONENT SIDE SHOWN



CONTACT LAYOUT



NOTES:

-  MATERIAL HOUSING : GREY GLASS FILLED POLYESTER
 : UL-RATING V0
 CONTACT : PHOSPHORBRONZE
-  GENERAL CONTACT PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT):
 1,27μm NICKEL MIN. AND ACTION PIN: 0,5μm TIN-LEAD MIN.
 FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION
 REFERENCE FOR EACH DASH NUMBER.
 REDUCED CROSS-TALK SHIELD: GOLD FLASH OVER 1,27μm NICKEL MIN.
-  CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
 PERFORMANCE LEVEL 2.
-  CONNECTOR ASSEMBLY WITH LATCH HINGE FOR CABLE CONNECTOR.
-  CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE
-  PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID.
-  PLATED SPOT ONLY ON COMPONENT SIDE, FORMING ONE CONTACT
 WITH PLATED THROUGH HOLES OF ROW C

P.C.B. HOLE DIM. ACTION PIN FIN. HOLE : 0,55 TO 0,65mm OTHER REQUIREMENTS SEE APPLICATION SPECIFICATION
--

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APPR
H	—		D	EH10-0680-05	06-06-05	BSV	BM
			D1	ECR-06-002635	07-02-06	BSV	BM
			E	ECR-06-026577	14-11-06	BSV	BM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.V.D.HEIJDEN 12FEB98	 Tyco Electronics Corporation s-Hertogenbosch, Netherlands,	
DIMENSIONS:		CHK D.TUREN 12FEB98	NAME	
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD F.V.KONINGSBRUGGE	Z-PACK 2MM HM TYPE C	
	0 PLC ± -	PRODUCT SPEC	55 POS. RIGHT ANGLE MALE CONNECTOR	
	1 PLC ± -	108-19082	WITH REDUCED CROSS-TALK SHIELDS	
	2 PLC ± -	APPLICATION SPEC		
	4 PLC ± -	114-19029		
ANGLES		SIZE	CAGE CODE	DRAWING NO
FINISH		WEIGHT	A2	00779
MATERIAL		C=352273		RESTRICTED TO
		CUSTOMER DRAWING		SCALE NTS
		SHEET 1 OF 1		REV F

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[352273-1](#)