



4

5

6

7

11.074 [.436]	500	ON TAPE	52265-3
11.074 [.436]	100	LOOSE PC	52265
WIRE INSULATION DIA MAX	QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED  
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL  
PRODUCT INFORMATION OR  
COPIES OF DRAWINGS  
AND TECHNICAL DOCUMENTS

FOR APPLICATION  
TOOLING INFORMATION

FOR ORDER ENTRY

PRODUCT INFORMATION CENTER  
1-800-522-6752

TOOLING ASSISTANCE CENTER  
1-800-722-1111

1-800-526-5142

MAX RECOMMENDED OPERATING  
TEMPERATURE:  
105° C [221°F]

VOLTAGE RATING:  
600 V MAX

CIRCULAR MIL AREA:  
10.54-16.77mm<sup>2</sup> [20,800-33,100]  
STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR  
AMP INCORPORATED. IT IS SUBJECT TO CHANGE  
AND THE CONTROLLING ENGINEERING ORGANIZATION  
SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm [INCHES]



TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

0 PLC ± -  
1 PLC ± -  
2 PLC ± -  
3 PLC ± 0.127[.005]  
4 PLC ± -  
ANGLES ± -

MATERIAL  
BODY:  
COPPER PER ASTM B-152  
INSULATION: PVC

FINISH  
BODY:  
TIN PLATE PER ASTM-B545  
INSULATION:  
COLOR: BLUE

DWN  
S.S. GOULDEN  
CHK  
R. HERSEY  
APVD  
M ELLIS  
PRODUCT SPEC  
UL 486A-B  
APPLICATION SPEC  
114-2161  
WEIGHT

9-29-93  
9-29-93  
9-29-93

 TE Connectivity Ltd.

NAME  
TERMINAL, RING TONGUE,  
PLASTI-GRIP  
WIRE SIZE: 6 AWG

SIZE  
A3

CAGE CODE  
00779

DRAWING NO  
C-52265

RESTRICTED TO  
—

CUSTOMER DRAWING

SCALE  
4:1

SHEET  
1 of 1

REV  
P5

1470-19 (1/15)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[52265-3](#)