




LOC	DIST	REVISIONS			
		ZONE	LTR	DESCRIPTION	DATE
G	14	P	F	REVISED & REDRAWN PER 0720-0040-93	3-29-93
			C	REACTIVATED 53833-1 PER 0720-6018-92	11/8 DAP



AMP		E13288	
WIRE RANGE		UL Listed	
16-14 AWG		16-14 AWG	
SOLID OR STRANDED		SOLID OR STRANDED	
LR7189 Certified		MILITARY P/N AND CLASS	
16-14 AWG		NOT APPLICABLE	
SOLID OR STRANDED			

△ STAMP BS AMP 16-14* APPROX AS SHOWN
BS INDICATES STUD SIZE



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: NOT APPLICABLE
FOR ORDER ENTRY	1-800-526-5142	WIRE CROSS SECTIONAL AREA RANGE: 1.04-2.62mm² [2,050-5,180] CIR MILS SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm (INCHES)
TOLERANCES ON:
2 PLC DEC # -
3 PLC DEC # -
ANGLES
MATERIAL
PHOSPHOR BRONZE
PER ASTM B-103
ANNEALED

FINISH
TIN PLATE
0.00254 [1.000100] MIN
THK PER MIL-T-10727

DR 3-29-93 TA BRINKMAN	NAME
CHK 3-29-93 DA PATTERSON	AMP
APPD 3-29-93 DE MILLER	AMP INCORPORATED Harrisburg, PA 17105-3608
APPD 3-29-93 JL MECKLEY	
PRODUCT SPEC	
APPLICATION SPEC	

TERMINAL, SHORT
SPRING SPADE, SOLISTRAND™

SIZE CAGE CODE DRAWING NO
SCALE 10:1 00779 53833

SHEET 1 OF 1

CUSTOMER DRAWING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[53833-1](#)