

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- . - .




COPYRIGHT — TE Connectivity Ltd.


ALL RIGHTS RESERVED.

## REVISIONS

| P  | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|----|-----|---------------------------|-----------|-----|------|
| E1 |     | REVISED PER ECO-10-025937 | 21DEC10   | HMR | DR   |
| E2 |     | REVISED PER ECO-17-016703 | 06APR2018 | RS  | DR   |



- 1 STAMP AMP 22-18\* APPROX AS SHOWN
- 2 WIRE INSULATION  $\phi 4.318[\phi.170]$  MAX.
- 3 NOTE DELETED



|      |              |           |
|------|--------------|-----------|
| 50   | LOOSE PIECE  | 8-55824-2 |
| 1000 | LOOSE PIECE  | 55824-1   |
| QTY  | PACKAGE TYPE | PART NO   |

AMP INCORPORATED  
CUSTOMER SERVICE SYSTEMSMAX RECOMMENDED OPERATING  
TEMPERATURE:

125° C[257°F] MAX

VOLTAGE RATING:  
600V MAX (BUILDING WIRING)  
1000V MAX (FIXTURES & SIGNS)CIRCULAR MIL AREA:  
0.26-0.96mm<sup>2</sup> [509-1900]  
STRANDEDFOR ADDITIONAL  
PRODUCT INFORMATION OR  
COPIES OF DRAWINGS  
AND TECHNICAL DOCUMENTSPRODUCT INFORMATION CENTER  
1-800-522-6752

FOR APPLICATION

TOOLING ASSISTANCE CENTER

TOOLING INFORMATION


1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR  
AMP INCORPORATED. IT IS SUBJECT TO CHANGE  
AND THE CONTROLLING ENGINEERING ORGANIZATION  
SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm [INCHES]MATERIAL  
BODY: ETP COPPER  
INSULATION: POLYOLEFINTOLERANCES UNLESS  
OTHERWISE SPECIFIED:  
0 PLC ± -  
1 PLC ± -  
2 PLC ± -  
3 PLC ± 0.127[.005]  
4 PLC ± -  
ANGLES ± -FINISH  
BODY: EDP TIN PLATED  
INSULATION: COLOR-RED

DWN 6/93

S S GOULDEN

CHK 6/93

R HERSEY

APVD 6/93

B BARE

PRODUCT SPEC

APPLICATION SPEC

408-4022

WEIGHT

CUSTOMER DRAWING



TE Connectivity Ltd.

NAME  
SPLICE, SEALABLE  
HEAT SHRINKABLE  
22-18 AWG

SIZE A3 CAGE CODE 00779 DRAWING NO C-55824 RESTRICTED TO -

SCALE NTS SHEET 1 OF 1 REV E2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[8-55824-2](#)