

4


3

2



1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		D	REV PER 0G3A-0256-04	08APR04	JR	TM


AMP WIRE RANGE	 Listed	 LR7189 Certified
22-14 AWG SOLID OR STRANDED	22-14 AWG SOLID OR STRANDED	22-14 AWG SOLID OR STRANDED

- △1 FOR 6.35 [.250] MAX WIRE INSULATION DIA.
- △2 MATERIAL: BODY: COPPER
INSULATION: NYLON
COLOR: BLACK
- △3 BODY: TIN PER ASTM B-545
- △4 PRELIMINARY - NOT FOR PRODUCTION



2500		TAPE MOUNTED		1-55927-0		4										
1000		LOOSE PIECE		55927-1												
QTY		DESCRIPTION			PART NO											
T.	DWN	1/93	<div>tyco</div> <div>Tyco Electronics Corporation</div> <div>Harrisburg, PA 17105</div>													
	G KRUPER															
	CHK	1/93	<div>Electronics</div>													
	R HERSEY															
	APVD	1/93	NAME SPLICE, WIRE, CLOSED END — —													
	T MICHIELUTTI															
	PRODUCT SPEC															
	—															
	APPLICATION SPEC		SIZE			CAGE CODE		DRAWING NO		RESTRICTED TO						
	—															
	WEIGHT	—	A3		00779		C-55927		—							
CUSTOMER DRAWING					SCALE		2:1		SHEET		1 OF 1		REV		D	

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 150° C
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 300V MAX
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 0.26-2.62mm ² [509-5180] SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH
MATERIAL — △2	— △3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[55927-1](#)