






**COPYRIGHT 2005
TE CONNECTIVITY CORP
ALL RIGHTS RESERVED**

FEMALE SCREWLOCKS	5745988-6
THREADED INSERTS	5745988-4
MOUNTING HARDWARE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 04-08-05 A. FERNANDEZ-DOCKS QW 04-08-05 J. GERMACE APVD M. WALMSLEY 04-08-05		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES (UNLESS OTHERWISE SPECIFIED): 9 PLC ± - 12 PLC ± - 15 PLC ± .005 18 PLC ± - ANGLES ± °		NAME RCPT ASSY, SIZE 1, RTANG, W/FRONT METAL SHELL, .026 DIA POSTS, AMPLIMITE HD-20 (.590 FOOTPRINT) SHORT LEG	
		PRODUCT SPEC 108-40025 APPLICATION SPEC 114-40010		SIZE A1	
MATERIAL 		FINISH 		CAGE CODE 00779	
		WEIGHT -		DRAWING NO C-5745988	
		CUSTOMER DRAWING		RESTRICTED TO	
				SCALE 4:1 SHEET 1 OF 1 REV P	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5745988-4](#)