






	PER DETAIL E		4.32	[.170]	1-5747299-6
	PER DETAIL E		3.18	[.125]	1-5747299-4
OBSOLETE	PER DETAIL E		3.18	[.125]	1-5747299-3
	PER DETAIL D		3.18	[.125]	5747299-8
			3.18	[.125]	5747299-7
			4.32	[.170]	5747299-4
	AS SHOWN		3.18	[.125]	5747299-2
	HARDWARE OPTIONS	CONTACTS	C		PART NO
		FINISH			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN B. LATUCCA 22SEP2005 ORK S. BOLASH 22SEP2005		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLC ± 1. PLC ± 2. PLC ± 0.15 [0.005] 3. PLC ± 14. PLG ± ANGLES ± ±		NAME RECEPTACLE ASSEMBLY, SIZE 2, 15 POSITION, FRONT METAL SHELL, WITH OR WITHOUT SCREWLOCKS OR INSERTS, AMPLIMITE HO-20	
MATERIAL 		FINISH 		SIZE CAGE CODE DRAWING NO A1 00779 C-5747299	
WEIGHT —		CUSTOMER DRAWING		RESTRICTED TO —	
				SCALE 4:1 SHEET 1 OF 1 REV B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-5747299-4](#)