







- 1
- HOUSING: FLAME RETARDANT, 94V-O RATED, GLASS FILLED, NYLON OR POLYESTER, COLOR: BLACK.
CONTACTS: BRASS.
INSERTS: ZINC.
- 2
- CONTACTS: SEE TABLE.
INSERTS: CLEAR CHROMATE COATING.
- 3
- REFER TO APPLICATION SPEC FOR RECOMMENDED P.C. BOARD MOUNTING DIMENSIONS FOR AUTOMATIC INSERTION.
- 4
- GOLD FLASH ON THE MATING SURFACES, .000100 MIN TIN ON THE SOLDER END, .000050 MIN NICKEL UNDERPLATE ON THE ENTIRE CONTACT.
- 5
- .000030 MIN GOLD PLATE ON THE MATING SURFACES, .000100 MIN TIN PLATE ON THE SOLDER END, .000050 MIN NICKEL UNDERPLATE ON THE ENTIRE CONTACT
-OR-
GOLD FLASH OVER PALLADIUM-NICKEL PLATE, .000030 MIN TOTAL ON THE MATING SURFACES, .000100 MIN TIN ON THE SOLDER END, .000050 MIN NICKEL UNDERPLATE ON THE ENTIRE CONTACT.

WITH INSERTS	5	5747467-4
WITH .120 DIA HOLE	5	5747467-2
WITH .120 DIA HOLE	4	5747467-1
REMARKS	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± 2°

MATERIAL

1

DWN C. PETERS 19SEP05

CHK S. BOLASH 19SEP05

APVD M. WALMSLEY 19SEP05

PRODUCT SPEC 108-40025

APPLICATION SPEC 114-40015

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

PLUG ASSY, SIZE 1, 9 POSN, RIGHT ANGLE, .590 SERIES, .026 DIA POSTS, AMPLIMITE HD-20

SIZE A1

CAGE CODE 00779

DRAWING NO 5747467

RESTRICTED TO -

SCALE 4:1

SHEET 1 OF 1

REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5747467-4](#)