

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT — TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	N	REV PER ECR 07-027142	13NOV07	JR	TM
	N1	REVISED PER ECO-17-016703	03APR2018	RS	DR
	N2	REVISED PER ECO-18-011826	26JUL2018	RS	DR

AMP

WIRE RANGE

12-10 AWG  
STRANDED

1

TUBING MATERIAL; CROSS-LINKED POLYMER WITH MELT LINER; COLOR, YELLOW; BLACK INK LEGEND 1/16 MIN; HEIGHT; ONE FULL APPEARANCE MIN.

2

TEMP RATING -65°F TO 257°F  
[-55°C TO 125°C ]

3

NOTE DELETED

4

SHIPPING WEIGHT .007 LBS EACH

5

VOLTAGE RATING: 600 V MAX  
( 1000 V MAX FIXTURES & SIGNS )

6

MATERIAL & FINISH ; BODY - COPPER, TIN PLATED  
SLEEVE - NYLON

7

NOTE DELETED

LOOSE PIECE	6.350 [.250]	2.921 [.115]	1000	603504-3
SMALL PACK	6.350 [.250]	2.921 [.115]	50/BOX	603504-2
PACKAGE TYPE	EXPANDED I.D. MIN	RECOVERED I.D. MAX	QTY	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm [INCHES]

MATERIAL

6

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± 0.127[.005]

4 PLC ± -

ANGLES ± -

FINISH

6

DWN JR RUTH 24JUN04

CHK T MICHIELUTTI 24JUN04

APVD T MICHIELUTTI 24JUN04

PRODUCT SPEC —

APPLICATION SPEC —

WEIGHT

TE Connectivity Ltd.

PRE-INSULATED SEALED SPLICE

WIRE SIZE: 12-10 AWG

—

SIZE A3

CAGE CODE 00779

DRAWING NO C-603504

RESTRICTED TO —

CUSTOMER DRAWING

SCALE 1:1

SHEET 1 OF 1

REV N2

8.992 [.354] MIN

47.498 [1.870] MAX

8.992 [.354] MIN

EXPANDED I.D

AMP 12-10

AMP 12-10

AMP 12-10

COPPER SPLICE

HEAT SHRINKABLE TUBING

1470-19 (1/15)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[603504-2](#)