


DWG NO. 604751

UNIT OF MEASURE	A	B	C	D	E	L		MAX. BUNDLE DIA.	MIN. TENSILE STRENGTH
INCHES	.275	.295	.183	2.37	.051	11.83		3.0	50 lbs.
MM	6.99	7.49	4.65	6.02	1.30	300.		76.2	22.68 kg.



NOTES:

1. MOISTURIZED 1 TO 2.5% WATER.
2. PACKAGED IN HEAT SEALED 3 MIL POLYBAG WITH LABEL PER DWG 404707.
3. MIL No. MS3367-7.

APC ENGINEERING

JUL 13 1990

ISSUED BY *Alca*CUSTOMER
DRAWING
UNPUBLISHED

2-604751-9	NATURAL 1000 TY3AM
2-604751-0	BLACK 1000 TY3AMB
1-604751-9	NATURAL 100 TY3AC
1-604751-0	BLACK 100 TYACB
604751-2	BLACK 1 (NO PKG.)
604751-1	NATURAL 1 (NO PKG.)

LOC D	DWG SIZE	PART No.	DESCRIPTION	ITEM NO
DIST 1	REVISION OF EACH ASSY NO. (WHEN BLANK, USE DWG REVISION)			
QTY. REQ'D. PER ASSY.		PARTS LIST		
		MATERIAL NYLON 6/6	HEAT TREAT	FINISH
		DIMENSIONS ARE IN INCHES	DRAWN BY: AD-TEK/VL	DATE: 6/26/90
		TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHECK BY: BJM 6/90	APPROVED BY:
		2 PL DEC ±	RELEASE:	7. HANDEL 6/90
		3 PL DEC ± .039	AMP INCORPORATED	
		4 PL DEC ±	Harrisburg, Pa.	
		ANGLES ±	NAME:	
		SURF TEXTURE: J	CABLE TIE 11-3/4 INCH	
		REMOVE BURRS, BREAK SHARP EDGES, .015 R. MAX.		
✓ B	ECN 062890	DATE: 6/90	SCALE: A	DRAWING No.: 604751
P	F	LTR	REVISION RECORD	APP DATE
			SHEET 1 OF 1	REV.: E

THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN AMP PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM AMP INCORPORATED, HARRISBURG, PA.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-604751-0](#)