

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	0	PROPOSED	-	-	-

AMP
WIRE RANGE12-10 AWG
SOLID OR STRANDED

- 1 STAMP AMP 12-10*, LOCATE APPROX AS SHOWN.
- 2 BODY - COPPER PER ASTM B-152
SLEEVE - COPPER PER ASTM B-152
INSULATION - NYLON
- 3 BODY - TIN PLATE PER ASTM B-545
SLEEVE - TIN PLATE PER ASTM B-545
INSULATION - COLOR , YELLOW
- 4 DIMENSION APPLIES FROM EDGE OF METAL WIRE BBL TO CENTER OF STUD.
- 5 WIRE INSULATION DIA .150-.250
- 6 TONGUE MATERIAL THK .042 MAX
- 7 PRELIMINARY - NOT FOR PRODUCTION

500

LOOSE PC

7 696715-1

QTY

DESCRIPTION

PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMSMAX RECOMMENDED OPERATING
TEMPERATURE:


105°C

VOLTAGE RATING:
300V MAX

CIRCULAR MIL AREA:

2.62-6.64mm² [5180-13100]
SOLID OR STRANDEDTHIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHESTOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .008
4 PLC ± -
ANGLES ± -
FINISH

MATERIAL

2

3

DWN jr ruth 06MAY04

CHK T MICHIELUTTI 06MAY04

APVD T MICHIELUTTI 06MAY04

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

tyco
ElectronicsTyco Electronics Corporation
Harrisburg, Pa 17105-3608NAME
TERMINAL, HOOK, P.I.D.G.,
WIRE SIZE 12-10 AWG

SIZE A3 CAGE CODE 00779 DRAWING NO C-696715 RESTRICTED TO -

SCALE 5:1 SHEET 1 OF 1 REV 0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[696715-1](#)