


LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			BI	REVISED PER ECO-11-005931	23MAR2011	HMR	CR



1 MATERIALS AND FINISH: HOUSING: PA 6-6, UL 94-V0, COLOR: SEE P/N TABLE. CLAMP: BRASS, NICKEL PLATED. DOUBLE SIDE CONTACT SPRING: PHOSPHOR BRONZE, TIN PLATED. CLAMPING SCREW: M3, BRASS, NICKEL PLATED. 2. WIRE SIZE RANGE SOLID WIRE: 12-30AWG STRANDED WIRE: 12-30AWG 3. RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC. FILE N° E60677. 4. IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1. 5 NOT CUMULATIVE TOLERANCE	GREEN	89.44	12	1-796981-2
	GREEN	81.82	11	1-796981-1
	GREEN	74.20	10	1-796981-0
	GREEN	66.58	9	796981-9
	GREEN	58.96	8	796981-8
	GREEN	51.34	7	796981-7
	GREEN	43.72	6	796981-6
	BLACK	36.10	5	2-796981-5
	GREEN	36.10	5	796981-5
	GREEN	28.48	4	796981-4
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: mm TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.001 4 PLC ±0.0001 ANGLES ±2 FINISH MATERIAL - DWN E. ZANOLINI CHK D. BIEVENOUR APVD D. BIEVENOUR 28MAR2001 28MAR2001 28MAR2001 PRODUCT SPEC - APPLICATION SPEC - WEIGHT - CUSTOMER DRAWING NAME TERMINAL BLOCK, PLUG 7.62mm PITCH - SIZE A2 CAGE CODE 00779 DRAWING NO C-796981 RESTRICTED TO - SCALE NTS SHEET 1 OF 1 REV BI	GREEN	20.86	3	796981-3
	GREEN	13.24	2	796981-2
	COLOR	DIM L.	NO OF POSN	PART NUMBER

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-796981-2](#)