









P	LTR	DESCRIPTION	DATE	DWN	APVD
B		REVISED (ECR-15-008999)	06JUL2015	SJ	HG
B1		REVISED (ECR-20-011402)	02SEP2020	CI	YJ
B2		REVISED (ECR-20-014410)	01DEC2020	CI	YJ
B3		REVISED (ECR-21-001740)	10FEB2021	CI	YJ

1-936394-3

x



0-936394-2





- NOTE
- 1.GENERAL TOLRANCE : ± 0.3 , $\pm 1^\circ$
- 2.0.15 MAX. WARPAGE AND 0.2 MAX. FLASH PERMISSIBLE
- 3.SURFACE DEFECTS ARE NOT ACCEPTABLE AS FOLLOW:
SINK, WELD LINES, HAIRCRACKS, SATIN & SCORES
- 4.APPLIED RECEPTACLE CONTACT P/N:

DESCRIPTION	2.8mm SENSOR-FLAT RECEPTACLE
PART NO.	967542 967543
WIRE SIZE (mm2)	0.5~1.0 1.25~2.5

- 5.APPLIED WIRE SEAL P/N:

DESCRIPTION	SINGLE-WIRE SEAL (5mm HOLE)
PART NO.	828904 828905
WIRE SIZE (mm2)	1.2~2.1 2.2~3.0



NO.	P/N	DESCRIPTION	COLOR	MATERIAL	QTY
4	936855-1	INNER SEAL	RED ORANGE	SILICONE (LSR)	1
3	1-936396-3	PROTECTOR HSG	GRAY	PA66-GF15	1
2	936396-2	PROTECTOR HSG	BLACK	PA66-GF15	1
1	936395-2	PLUG HSG	BLACK	PA66-GF15	1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.J. CHOI	TE Connectivity		
DIMENSIONS: mm		CHK J.W. JUNG			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC $\pm$ 1 PLC ± 0.1 2 PLC ± 0.01 3 PLC ± 0.001 4 PLC ± 0.0001 ANGLES $\pm$ FINISH		APVD H.G. CHO	NAME 2.8mm SEALED 6P PLUG ASSEMBLY		
MATERIAL SEE TABLE		APPLICATION SPEC	SIZE A2		
		WEIGHT	CAGE CODE 00779		
		CUSTOMER DRAWING	DRAWING NO C=936394		
			RESTRICTED TO -		
			SCALE 1:1		
			SHEET 1 OF 1		
			REV B3		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[936394-2](#)