

REV. B  
DCO 300825


TOLERANCES  $\pm .010"$  - UNLESS  
OTHERWISE SPECIFIED

COIL: @ 25°C  
RESISTANCE 400 OHMS  $\pm 10\%$   
NOMINAL VOLTAGE 28 VDC  
MUST OPERATE 13.5 VDC MAX.  
MUST RELEASE 5.5 VDC MAX., 2.3 VDC MIN.

ENVIRONMENT:  
VIBRATION 70 Hz TO 3000 Hz @ 30 g's  
SHOCK 200 g's 6 MS. DURATION  
TEMPERATURE -70 °C TO +125 °C

NOTES: OPERATE, RELEASE 6 MS MAX.  
CONTACT STABILIZATION 2.5 MS MAX.  
CONTACT BOUNCE 1 MS MAX.

## CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL  
5 AMPS 28 VDC, 115 VAC 400 Hz RESISTIVE  
100,000 OPERATIONS

DR. B.D. 25APR2008 CK. 5/9/08 J.M.B.

**Tyco Electronics**

©COPYRIGHT 2005  
TYCO ELECTRONICS CORPORATION  
ALL INTERNATIONAL RIGHTS RESERVED

CUST. M83536/5-020M  
CUST. NO. ---- REV. ---

TE NUMBER  
6-1617760-6

CII PART NUMBER  
FCB-405-0520M

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-1617760-6](#)