

REV. B  
DCO 300825

TOLERANCES  $\pm .010$ " - UNLESS  
OTHERWISE SPECIFIED

COIL: @ 25°C  
RESISTANCE 78 OHMS  $\pm 10\%$   
NOMINAL VOLTAGE 12 VDC  
MUST OPERATE 6.6 VDC MAX.  
TRANSIENT SUPPRESSION - 42 VDC MAX.  
MUST RELEASE 3.3 VDC MAX., 0.75 VDC MIN.


ENVIRONMENT:  
VIBRATION 70 Hz TO 3000 Hz @ 30 g's  
SHOCK 200 g's 6 MS. DURATION  
TEMPERATURE -70 °C TO +125 °C

NOTES: OPERATE, RELEASE 6 MS MAX.  
CONTACT STABILIZATION 2.5 MS MAX.  
CONTACT BOUNCE 1 MS MAX.  
CONTACT BREAK BOUNCE 0.1 MS MAX.

CUST. M83536/6-012L  
CUST. NO. ---- REV. ---

TE NUMBER  
7-1617760-3

## CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL  
5 AMPS 28 VDC, 115 VAC 400 Hz RESISTIVE  
100,000 OPERATIONS

DR. B.D. 25APR2008 CK. 5/9/08 J.M.B.

**Tyco Electronics**

©COPYRIGHT 2005  
TYCO ELECTRONICS CORPORATION  
ALL INTERNATIONAL RIGHTS RESERVED

CII PART NUMBER  
FCB-405-0612L

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[7-1617760-3](#)