

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT 2020 TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL CUSTOMER DRAWING	30JAN2020	AFK	LS


FLATTENED WIDTH



D

d


w



SPOOL

EXPANDED TUBING PRODUCT

SPOOL I.D. 101 (4.0)




Product Size	2.4	3.2	4.8	6.4	9.5	12.7	19.0	25.4	38.1
"D" Minimum Supplied I.D.	2.40 (.094)	3.20 (.126)	4.80 (.187)	6.35 (.250)	9.5 (.374)	12.7 (.500)	19.05 (.750)	25.4 (1.00)	38.1 (1.50)
"d" Maximum Recovered I.D.	1.19 (.047)	1.60 (.063)	2.40 (.094)	3.20 (.126)	4.80 (.189)	6.40 (.250)	9.50 (.374)	12.7 (.500)	19.05 (.750)
"w" Recovered Wall Thickness	0.50±0.10 (.020±.004)	0.50±0.10 (.020±.004)	0.51±0.11 (.020±.004)	0.65±0.15 (.026±.006)	0.65±0.15 (.026±.006)	0.65±0.15 (.026±.006)	0.75±0.15 (.030±.006)	0.90±0.15 (.035±.006)	1.00±0.20 (.039±.008)
Minimum Sleeve Flattened Width	4.90 (.193)	6.50 (.256)	8.90 (.350)	11.0 (.430)	15.7 (.618)	20.7 (.815)	30.7 (1.209)	41.1 (1.620)	61.0 (2.40)

NOTES:
1. ALL DIMENSIONS ARE IN MILLIMETERS (inches).

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

DWN AFK 30JAN2020

CHK -

APVD LS 30JAN2020

PRODUCT SPEC RW-2536

APPLICATION SPEC -

WEIGHT VARIOUS

CUSTOMER DRAWING

TE Connectivity

NAME ZHD-CT OUTSIDE PRINTER SPOOL

SIZE A3

CAGE CODE 0198G

DRAWING NO C-MCD170008

RESTRICTED TO -

SCALE -

SHEET 1 OF 1

REV B

1470-19 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EL8114-000](#)