

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT 2020 TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL CUSTOMER DRAWING	30JAN2020	AFK	LS


FLATTENED WIDTH




D

d


w




EXPANDED TUBING PRODUCT



SPOOL



SPOOL I.D.
101 (4.0)




Product Size	2.4	3.2	4.8	6.4	9.5	12.7	19.0	25.4	38.1
"D" Minimum Supplied I.D.	2.40 (.094)	3.20 (.126)	4.80 (.187)	6.35 (.250)	9.5 (.374)	12.7 (.500)	19.05 (.750)	25.4 (1.00)	38.1 (1.50)
"d" Maximum Recovered I.D.	1.19 (.047)	1.60 (.063)	2.40 (.094)	3.20 (.126)	4.80 (.189)	6.40 (.250)	9.50 (.374)	12.7 (.500)	19.05 (.750)
"w" Recovered Wall Thickness	0.50±0.10 (.020±.004)	0.50±0.10 (.020±.004)	0.51±0.11 (.020±.004)	0.65±0.15 (.026±.006)	0.65±0.15 (.026±.006)	0.65±0.15 (.026±.006)	0.75±0.15 (.030±.006)	0.90±0.15 (.035±.006)	1.00±0.20 (.039±.008)
Minimum Sleeve Flattened Width	4.90 (.193)	6.50 (.256)	8.90 (.350)	11.0 (.430)	15.7 (.618)	20.7 (.815)	30.7 (1.209)	41.1 (1.620)	61.0 (2.40)

NOTES:
1. ALL DIMENSIONS ARE IN MILLIMETERS (inches).

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

DWN
AFK
CHK
-

30JAN2020

APVD
LS


30JAN2020

PRODUCT SPEC
RW-2536

APPLICATION SPEC
-

WEIGHT
VARIOUS

CUSTOMER DRAWING

TE Connectivity

ZHD-CT
OUTSIDE PRINTER SPOOL

-

SIZE
A3

CAGE CODE
0198G

DRAWING NO
C-MCD170008

RESTRICTED TO
-

SCALE
-

SHEET
1 OF 1

REV
B

1470-19 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EL8119-000](#)