


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	2	INITIAL CUSTOMER DRAWING	20JAN2020	AFK	LS



Product Size	2.4	3.2	4.8	6.4	9.5	12.7	19.0	25.4	38.1
"D" Minimum Supplied I.D.	2.40 (.094)	3.20 (.126)	4.80 (.189)	6.40 (.252)	9.50 (.374)	12.7 (.500)	19.0 (.748)	25.4 (1.00)	38.1 (1.50)
"d" Maximum Recovered I.D.	1.20 (.047)	1.60 (.063)	2.40 (.094)	3.20 (.126)	4.80 (.189)	6.4 (.252)	9.50 (.374)	12.7 (.500)	19.1 (.750)
"w" Recovered Wall Thickness	0.50±0.10 (.020±.004)	0.50±0.10 (.020±.004)	0.51±0.11 (.020±.004)	0.65±0.15 (.026±.006)	0.65±0.15 (.026±.006)	0.65±0.15 (.026±.006)	0.75±0.15 (.030±.006)	0.90±0.15 (.035±.006)	1.00±0.20 (.039±.008)
Minimum Sleeve Flattened Width	5.90 (.232)	6.50 (.256)	8.90 (.350)	11.0 (.433)	15.7 (.618)	20.7 (.815)	30.7 (1.209)	41.1 (1.618)	61.0 (2.402)

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS (inches).

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm

MATERIAL  
CROSSLINKED POLYOLEFIN

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

DWN AFK 15JAN2020

CHK -

APVD LS 20JAN2020

PRODUCT SPEC RW-2072

APPLICATION SPEC -

WEIGHT VARIOUS

CUSTOMER DRAWING

TE Connectivity

NAME HX-CT  
OUTSIDE PRINTER SPOOL

SIZE A3CAGE CODE 0198GDRAWING NO C-MCD170013RESTRICTED TO -

SCALE -SHEET 1 OF 1REV 2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EL8211-000](#)