



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	2	INITIAL CUSTOMER DRAWING	20JAN2020	AFK	LS



Product Size	2.4	3.2	4.8	6.4	9.5	12	18	25	38
"D" Minimum Supplied I.D.	2.4 (.094)	3.2 (.126)	4.8 (.189)	6.4 (.252)	9.5 (.374)	12.7 (.500)	19.1 (.752)	25.4 (1.00)	38.1 (1.50)
"d" Maximum Recovered I.D.	0.8 (.031)	1.1 (.043)	1.6 (.063)	2.1 (.083)	3.2 (.126)	4.2 (.165)	6.4 (.252)	8.5 (.335)	19.1 (.752)
"w" Recovered Wall Thickness ±0.08 (.003)	0.51 (.020)	0.51 (.020)	0.58 (.023)	0.58 (.023)	0.61 (.024)	0.61 (.024)	0.61 (.024)	0.64 (.025)	0.64 (.025)
Minimum Sleeve Flattened Width	4.30 (.169)	5.82 (.229)	8.00 (.315)	10.65 (.419)	15.5 (.610)	20.4 (.803)	30.5 (1.201)	40.4 (1.591)	60.3 (2.374)

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS (inches).

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AFK CHK —	09JAN2020 —	TE Connectivity		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD LS	20JAN2020	NAME D—CT OUTSIDE PRINTER SPOOL —		
	0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —	PRODUCT SPEC RW—2519		SIZE	CAGE CODE	DRAWING NO
		APPLICATION SPEC —		—	—	—
MATERIAL CROSSLINKED POLYOLEFIN	FINISH —	WEIGHT VARIOUS	A30198G	C=MCD170014		RESTRICTED TO —
CUSTOMER DRAWING				SCALE —	SHEET 1 OF 1	REV 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EL8084-000](#)