


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE PER ECO-19-010993	7/12/2019	J.B.	T.L.

RAYCHEM RW-175 Tubing SCD

Table 1: Dimensions mm(*inches*)

Size	As Supplied		As Recovered							
	Inside Diameter		Inside Diameter		Wall Thickness					
	Minimum		Maximum		Minimum		Maximum		Nominal	
	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.
3/64	1.17	0.046	0.58	0.023	0.20	0.008	0.31	0.012	0.25	0.010
1/16	1.60	0.063	0.79	0.031	0.20	0.008	0.31	0.012	0.25	0.010
3/32	2.36	0.093	1.17	0.046	0.20	0.008	0.31	0.012	0.25	0.010
1/8	3.18	0.125	1.58	0.062	0.20	0.008	0.31	0.012	0.25	0.010
3/16	4.75	0.187	2.36	0.093	0.20	0.008	0.31	0.012	0.25	0.010
1/4	6.35	0.250	3.18	0.125	0.28	0.011	0.38	0.015	0.33	0.013
3/8	9.53	0.375	4.75	0.187	0.28	0.011	0.38	0.015	0.33	0.013
1/2	12.70	0.500	6.35	0.250	0.28	0.011	0.38	0.015	0.33	0.013
3/4	19.05	0.750	9.53	0.375	0.36	0.014	0.51	0.020	0.43	0.017
1	25.40	1.000	12.70	0.500	0.41	0.016	0.56	0.022	0.48	0.019
1-1/2	38.10	1.500	19.05	0.750	0.43	0.017	0.58	0.023	0.51	0.020
2	50.80	2.000	25.40	1.000	0.43	0.017	0.58	0.023	0.51	0.020

Color: Standard Clear (Translucent light tan)
Non-Standard Black

Reference Specification 108-120022

THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

© COPYRIGHT 2019 TE Connectivity Ltd.

DIMENSIONS:		DWN	12-Mar-2019	MATERIAL		FINISH	
INCHES		J. Bitter		-		-	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	-	 TE Connectivity Ltd.			
		T. Licko	-				
		APVD	-				
		T. Licko	-				
0 PLC ± -		PRODUCT SPEC		NAME			
1 PLC ± -		108-120022					
2 PLC ± -		APPLICATION SPEC		RAYCHEM RW-175 TUBING SCD			
3 PLC ± -		-					
4 PLC ± -		WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
ANGLES ± -		-		A4	06090	©-RW-175	-
CUSTOMER DRAWING				SCALE	1:1	SHEET	1 OF 1
				REV A			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[M23053/8-011-C](#)