




PART NUMBER	CRIMP ID	Ø A ±.13 [.005]	Ø B ±.13 [.005]	Ø C ±.13 [.005]	CONDUCTOR WIRE SIZE REF 	WEIGHT REF GR [OZ]
SRK-PC-080-16-XX	A	8.10 [.319]	5.20 [.205]	9.59 [.378]	16mm ² 6 AWG	16.26 [.574]
SRK-PC-080-20-XX	B	8.10 [.319]	5.80 [.228]	9.59 [.378]	5 AWG	15.65 [.552]
SRK-PC-080-25-XX	C	9.50 [.374]	6.90 [.272]	9.50 [.374]	25mm ² 4 AWG	16.51 [.582]
SRK-PC-080-32-XX	D	11.30 [.445]	8.00 [.315]	9.59 [.374]	2 AWG	18.36 [.648]
SRK-PC-080-35-XX	E	12.00 [.472]	8.90 [.350]	9.59 [.374]	35mm ²	18.34 [.647]



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			NC	NEW RELEASE PER E.O. P20459	05MAR2010	DAVID MEYER	BBR
			A	REVISED PER E.O. P20612	09SEP2010	DM	RDR
			A1	REVISED PER ECO-15-012830	17SEP2015	JA	DM
			B	REVISED PER PCN-21-001241	12FEB2021	CL	IG



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID G. MEYER 05MAR2010	 TE Connectivity								
		CHK DAVID G. MEYER 09SEP2010									
		APVD ROBIN REED 09SEP2010	NAME CONTACT, SOCKET 8mm DIA SRK SERIES								
DIMENSIONS: mm [INCHES]		PRODUCT SPEC N/A									
		0 PLC ±	SIZE A3			CAGE CODE 4AFU8		DRAWING NO C-SRK-PC-080-16/35-XX		RESTRICTED TO -	
		1 PLC ±									
2 PLC ±0.64 [.025]											
3 PLC ±											
4 PLC ±											
MATERIAL COPPER ALLOY		ANGLES ±0°30'0"	APPLICATION SPEC 114-151039		SCALE 2:1						
FINISH 		WEIGHT	Customer Drawing								SHEET 1

 WHEN XX = 601: PLATING IS SILVER AND MAY TARNISH.
NOTES: UNLESS OTHERWISE SPECIFIED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[SRK-PC-080-16-601](#)