




PART NUMBER	CRIMP ID	ØA ±.13 [.005]	ØB ±.13 [.005]	ØC ±.13 [.005]	CONDUCTOR WIRE SIZE REF 	WEIGHT REF GR [OZ]
SRK-SC-080-16-XX	A	8.10 [.319]	5.20 [.205]	9.59 [.378]	16mm ² 6 AWG	12.53 [.442]
SRK-SC-080-20-XX	B	8.10 [.319]	5.80 [.228]	9.59 [.378]	5 AWG	11.91 [.420]
SRK-SC-080-25-XX	C	9.50 [.374]	6.90 [.272]	9.50 [.374]	25mm ² 4 AWG	12.76 [.450]
SRK-SC-080-32-XX	D	11.30 [.445]	8.00 [.315]	9.59 [.374]	2 AWG	14.59 [.515]
SRK-SC-080-35-XX	E	12.00 [.472]	8.90 [.350]	9.59 [.374]	35mm ²	14.55 [.513]



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
			NC	NEW RELEASE PER E.O. P20459	05MAR2010	DM RDR
			A	REVISED PER E.O. P20612	09SEP2010	DM RDR
			A1	REVISED PER ECO-15-012830	17SEP2015	JA DM



-  WHEN XX = 601: PLATING IS SILVER AND MAY TARNISH.
-  MATERIAL: SOCKET BODY & INSERT: COPPER.
-  FOR CRIMPING INFORMATION SEE DRAWING 8925-003-0000.

NOTES: UNLESS OTHERWISE SPECIFIED

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID MEYER 05MAR2010	 TE Connectivity	
DIMENSIONS: mm[INCHES]		CHK DAVID MEYER 09SEP2010		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD ROBIN REED 09SEP2010	NAME CONTACT, SOCKET 8mm DIA SRK SERIES	
		PRODUCT SPEC N/A	SIZE A3	
MATERIAL		APPLICATION SPEC 8925-003-0000	CAGE CODE 4AFU8	DRAWING NO SRK-SC-080-16/35-XX
FINISH 		WEIGHT	RESTRICTED TO	REV A1
		Customer Drawing	SCALE 2:1	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[SRK-SC-080-16-601](#)