

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	18JAN2016	N.P	X.X
	A1	PER ECR-16-010253	21JUL2016	N.P	X.X
	A2	ECR-20-011067 TYPE MODIFY	05AUG2020	S.C	C.W





TABLE 1			THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN Nick Pan 09DEC2015				TE Connectivity			
TECHNICAL DATA	T40514X0003-00X	T40514X0004-00X	DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK Kobby Zhao 09DEC2015		APVD Xiang Xu 09DEC2015		NAME M8 CABLE ASSEMBLY SINGLE ENDED FEMALE SIDE, UNSHIELDED			
RATED VOLTAGE	60V	30V	mm		0 PLC $\pm$ -		PRODUCT SPEC		108-106140		SIZE		CAGE CODE	
RATED CURRENT		3A			1 PLC ± 0.35		APPLICATION SPEC		-		DRAWING NO		RESTRICTED TO	
POLLETION DEGREE		3			2 PLC ± 0.25						A2		-	
OVERVOLTAGE CATEGORY		II			3 PLC $\pm$						© T40514X000X00X			
MATERIAL GROUP		II			4 PLC $\pm$									
DEGREE OF PROTECTION		IP67			ANGLES $\pm$									
			MATERIAL		FINISH									
			TBD		-									
							WEIGHT		-					
							CUSTOMER DRAWING				SCALE 1:1		SHEET 1 OF 1	
													REV A2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4051420004-002](#)