



TABLE 1

TECHNICAL DATA	T40521X4003-00X	T40521X4004-00X
RATED VOLTAGE	60V	30V
RATED CURRENT	3A	
POLLETION DEGREE	3	
OVERVOLTAGE CATEGORY	II	
MATERIAL GROUP	II	
DEGREE OF PROTECTION	IP67	

NOTES:

1. TECHNICAL DATA: SEE TABLE 1

2. RECOMMEND TORQUE 0.4Nm

3. TE LABLE AREA.

4. -*: CABLE LENGHT. -0.5:0.5m, -1.0:1.0m, -1.5:1.5m...

5. INSERT MARK FOR MATING.

6. ALL PRODUCT MUST COMPLIANCE WITH ROHS AND REACH.

VIEW A

T40521X4003-00X

T40521X4004-00X

VIEW B

T40521X4003-00X

T40521X4004-00X

COMMENTS	MATERIAL	DESCRIPITON	ITEM
		TE LABLE	10
		CABLE	9
	COPPER ALLOY	NUT	8
	RUBBER	O-RING	7
	PA66	HOUSING	6
	COPPER ALLOY	CONTACT	5
	POLYURETHANE	OVER-MOLDING	4
-	COPPER ALLOY	COUPLING NUT	3
BALCK COLOR	PA66	HOUSING	2
GOLD FLASH	COPPER ALLOY	CONTACT	1

WIRE CHARACTERISTIC	WIRE	TEMPERATURE	JACKET COLOR	JACKET MATERIAL	TYPE	POS.	PART NUMBER
WIRES: 0.25mm ² (24AWG)	-001: 0.5m	FIXED: -25°C~80°C	GRAY	PUR (UL)	RPC-M8-4MS-***-M8-4FR-PUR	4	T4052124004-00X
	-002: 1.0m	FLXIBLE: -10°C~80°C			RPC-M8-3MS-***-M8-3FR-PUR	3	T4052124003-00X
	-003: 1.5m						
	-004: 3.0m	FIXED: -10°C~80°C	BLACK	PVC (UL)	RPC-M8-4MS-***-M8-4FR-PVC	4	T4052114004-00X
	-005: 5.0m	FLXIBLE: -5°C~80°C			RPC-M8-3MS-***-M8-3FR-PVC	3	T4052114003-00X
	-006: 7.0m						
	-007: 10.0m						

THIS DRAWING IS A CONTROLLED DOCUMENT.	DWN	CHK	APVD	NAME
	Nick Pan	Kobby Zhao	Xiang Xu	

PRODUCT SPEC	APPLICATION SPEC	WEIGHT	CUSTOMER DRAWING
108-106140	-	-	

SCALE	SHEET	OF	REV
1:1	1	1	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4052114004-002](#)