





6. 产品必须符合ROHS与REACH.

		TE LABLE	10
		CABLE	9
	COPPER ALLOY	NUT	8
	RUBBER	O-RING	7
	PA66	HOUSING	6
	COPPER ALLOY	CONTACT	5
	POLYURETHANE	OVER-MOLDING	4
-	COPPER ALLOY	COUPLING NUT	3
BALCK COLOR	PA66	HOUSING	2
GOLD FLASH	COPPER ALLOY	CONTACT	1
COMMENTS	MATERIAL	DESCRIPITON	ITEM

WIRES: 0.25mm ² (24AWG)	-001: 0.5m -002: 1.0m -003: 1.5m -004: 3.0m	FIXED: -25°C~80°C FLXIBLE: -10°C~80°C	GRAY	PUR (UL)	RPC-M8-4MR-***-M8-4FS-PUR 	4	T4052223004-00X	
	-005: 5.0m -006: 7.0m -007: 10.0m	FIXED: -10°C~80°C FLXIBLE: -5°C~80°C			RPC-M8-3MR-***-M8-3FS-PUR 	3	T4052223003-00X	
				BLACK	PVC (UL)	RPC-M8-4MR-***-M8-4FS-PVC 	4	T4052213004-00X
						RPC-M8-3MR-***-M8-3FS-PVC 	3	T4052213003-00X
CABLE CHARACTERISTIC	LENGTH "L"	RECOMMEND OPERATION TEMPERATURE FOR CABLE	JACKET COLOR	JACKET MATERIAL	TYPE	POS.	PART NUMBER	



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Nick Pan 25FEB2016 CHK Kobby Zhao 25FEB2016 APVD Kiang Xu 25FEB2016		 TE Connectivity			
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.5 2 PLC ±0.35 3 PLC ± 4 PLC ± ANGLES ± FINISH -		NAME M8 CABLE ASSEMBLY UNSHIELDED TYP DOUBLE ENDED -			
MATERIAL TBD material 2 finish spec 2		PRODUCT SPEC 108-106140 APPLICATION SPEC - WEIGHT -		SIZE A2 CAGE CODE - DRAWING NO C-T40522X300X00X		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 1:1	SHEET 1 of 1	REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4052213004-006](#)