


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION






© COPYRIGHT copyright.d8Ye-

ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW RELEASE PER ECR-18-012916	22OCT2018	AZ	CW




SCALE 1:1





THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ALEX ZHANG 31JUL2018	TE Connectivity			
		CHK HART HE 31JUL2018				
DIMENSIONS:		APVD CHRIS WANG 31JUL2018	NAME CABLE JUMPER, UNSHIELDED M8 MR TO M12 FS OR FR, A-CODE			
mm		PRODUCT SPEC 108-106140	SIZE A2		CAGE CODE -	DRAWING NO C-T40522XX00XXXX
		APPLICATION SPEC 114-137144			RESTRICTED TO -	
MATERIAL -		WEIGHT -				
material_2		finish_spec_2	CUSTOMER DRAWING		SCALE 2:1	SHEET 1 OF 3
					REV A	


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



SCALE 1:1



T40522X8003-00X AS SHOWN



T40522X8004-00X AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ALEX ZHANG 31JUL2018	 TE Connectivity			
		CHK HART HE 31JUL2018				
DIMENSIONS: mm		APVD CHRIS WANG 31JUL2018	NAME CABLE JUMPER, UNSHIELDED M8 MR TO M12 FS OR FR, A-CODE -			
		PRODUCT SPEC 108-106140				
		APPLICATION SPEC 114-137144	SIZE A2	CAGE CODE -	DRAWING NO C-T40522XX00XXXX	RESTRICTED TO -
MATERIAL -	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	FINISH -	WEIGHT -			
material_2	finish_spec_2	CUSTOMER DRAWING	SCALE 2:1		SHEET 2 OF 3	REV A

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT copyright.dbye-

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

TABLE 1

TECHNICAL DATA	T4052217003-00X	T4052227003-00X	T4052218003-00X	T4052228003-00X	T4052217004-00X	T4052227004-00X	T4052218004-00X	T4052228004-00X
RATED VOLTAGE	60V				30V			
RATED CURRENT	3A							
POLLUTION DEGREE	3							
OVERVOLTAGE CATEGORY	II							
MATERIAL GROUP	II							
DEGREE OF PROTECTION	IP67							

TABLE 2

WIRES: 0.25mm ² (24AWG) WIRE COLOR: 1-BROWN, 2-WHITE, 3-BLUE, 4-BLACK OD: APROX. 5.0MM	STANDARD: -001: 0.5m -002: 1.0m -003: 1.5m -004: 3.0m -005: 5.0m -006: 7.0m -007: 10.0m CUSTOMIZATION: -99X:<1.0M -XXX:>1.0M -AAX:99.XM EXAMPLE: -035=3.5M -150=15.0M -994=0.4M	FIXED: -40°C~80°C FLXIBLE: -25°C~80°C	GRAY	PUR (UL)	RPC-M8-4MR-**-M12-4FR-PUR	4	T4052228004-00X
					RPC-M8-4MR-**-M12-4FS-PUR	4	T4052227004-00X
					RPC-M8-3MR-**-M12-3FR-PUR	3	T4052228003-00X
					RPC-M8-3MR-**-M12-3FS-PUR	3	T4052227003-00X
					RPC-M8-4MR-**-M12-4FR-PVC	4	T4052218004-00X
					RPC-M8-4MR-**-M12-4FS-PVC	4	T4052217004-00X
					RPC-M8-3MR-**-M12-3FR-PVC	3	T4052218003-00X
					RPC-M8-3MR-**-M12-3FS-PVC	3	T4052217003-00X
CABLE CHARACTERISTIC	LENGTH "L"	CABLE TEMP. RANGE	JACKET COLOR	JACKET MATERIAL	TYPE	POS.	PART NUMBER

NOTES:

1. TECHNICAL DATA: SEE TABLE 1

CODE POSITION INDICATOR

RECOMMEND TORQUE 0.4Nm

RECOMMEND TORQUE 0.6Nm

TE LABLE AREA.INCLUDING PN,DATE CODE...

-00X: FOR CABLE LENGHT,SEE TABLE 2 AND REFFER TO LENGTH "L"

-** :CABLE LENGTH,-0.5:0.5M;-1.0:1.0M;-1.5:1.5M

8. CABLE ASSEMBLY TO BE PACKAGED IN POLYBAGS;

注意事项

1. 技术参数：见表1

CODE 位置指示；

推荐扭矩0.4 Nm；

推荐扭矩0.6 Nm；

TE 标签位置 包含产品编号 日期代码。。。；

-00X：线长参考表2 参照长度"L"

-**：线长，-0.5:0.5M;-1.0:1.0M;-1.5:1.5M

8. 线缆组件塑料袋包装；

BLACK	PA66	END CAP	12
BLUE	TPU	M12 OVER-MOLDING	11
GOLD FLASH	COPPER ALLOY	FEMALE CONTACT	10
GRAY	SILICONE	O-RING	9
NICKEL PLATED	COPPER ALLOY	M12, FEMALE NUT	8
BLACK	PA66	M12, FEMALE HSG, A CODE, 5PINS	7
-	-	CABLE	6
-	-	TE LABLE	5
BLUE	TPU	M8 RA OVERMOLDING	4
GOLD FLASH	COPPER ALLOY	M8 MALE CONTACT	3
NICKEL PLATED	COPPER ALLOY	M8 MALE NUT	2
BALCK COLOR	PA66	M8 MALE HOUSING	1
COMMENTS 备注	MATERIAL 材质	DESCRIPTION 描述	ITEM NO 序号

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

material_2

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH -

±
±
±
±
±
±
-

DWN
ALEX ZHANG
CHK
HART HE
APVD
CHRIS WANG

31 JUL 2018
31 JUL 2018
31 JUL 2018

PRODUCT SPEC
108-106140
APPLICATION SPEC
114-137144
WEIGHT
-

TE Connectivity

NAME
CABLE JUMPER,UNSHIELDED
M8 MR TO M12 FS OR FR,A-CODE
-

SIZE
A2

CAGE CODE
-

DRAWING NO
 T40522XX00XXXX

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
2:1

SHEET
3 OF 3

REV
A

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4052217003-004](#)