


D




C

B

A



SCALE 1:1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ALEX ZHANG 31JUL2018	TE Connectivity							
		CHK HART HE 31JUL2018								
		APVD CHRIS WANG 31JUL2018	NAME CABLE JUMPER, UNSHIELDED M8 FR TO M12 MS OR MR, A-CODE							
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO
mm		0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH		108-106140 114-137144		A2		-	©-T40524XX00XXXX	-
MATERIAL		-		WEIGHT		-		CUSTOMER DRAWING		
						SCALE 1:1		SHEET 1 OF 3		REV A

D

C

B

A


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT copyright.d8Ye-

ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



SCALE 1:1



T40524X600X-00X AS SHOWN

SIDE 1 M8X1

SIDE 2 M12X1

	T40524X6003-00X	T40524X6004-00X
SIDE 1		
SIDE 2		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN31JUL2018

CHK31JUL2018

APVD31JUL2018

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

ALEX ZHANG

HART HE

CHRIS WANG

108-106140

114-137144

-

TE Connectivity

CABLE JUMPER, UNSHIELDED
M8 FR TO M12 MS OR MR, A-CODE

SIZEA2

CAGE CODE-

DRAWING NO.C-T40524XX00XXXX

RESTRICTED TO-

SCALE1:1

SHEET2 OF 3

REVA

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT copyright.dBye-

ALL RIGHTS RESERVED.

TABLE 1

TECHNICAL DATA	T4052415003-00X	T4052425003-00X	T4052416003-00X	T4052426003-00X	T4052415004-00X	T4052425004-00X	T4052416004-00X	T4052426004-00X
RATED VOLTAGE	60V				30V			
RATED CURRENT	3A							
POLLUTION DEGREE	3							
OVERVOLTAGE CATEGORY	II							
MATERIAL GROUP	II							
DEGREE OF PROTECTION	IP67							

NOTES:

1. TECHNICAL DATA: SEE TABLE 1

2

CODE POSITION INDICATOR

3

RECOMMEND TORQUE 0.4Nm

4

RECOMMEND TORQUE 0.6Nm

5

TE LABLE AREA.INCLUDING PN,DATE CODE...

6

-00X: FOR CABLE LENGHT,SEE TABLE 2 AND REFFER TO LENGTH "L"

7

-*:CABLE LENGTH,-0.5:0.5M;-1.0:1.0M;-1.5:1.5M

8. CABLE ASSEMBLY TO BE PACKAGED IN POLYBAGS;

WIRING DIAGRAM

POLE NO.	M8 A CODE	M12 A CODE
1	BROWN	BROWN
2	WHITE	WHITE
3	BLUE	BLUE
4	BLACK	BLACK

TE Connectivity

CABLE JUMPER,UNSHIELDED

M8 FR TO M12 MS OR MR,A-CODE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

-

©T40524XX00XXXX

-

CUSTOMER DRAWING

SCALE 1:1

SHEET 3 OF 3

REV A

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

TABLE 2

WIRES: 0.25mm ² (24AWG) WIRE COLOR:1-BROWN,2-WHITE, 3-BLUE,4-BLACK OD: APROX. 5.0MM	STANDARD: -001: 0.5m -002: 1.0m -003: 1.5m -004: 3.0m -005: 5.0m -006: 7.0m -007: 10.0m CUSTOMIZATION: -99X:<1.0M -XXX:>1.0M -AAX:99.XM EXAMPLE:-035=3.5M -150=15.0M -994=0.4M	FIXED: -40°C~80°C FLXIBLE: -25°C~80°C	GRAY	PUR (UL)	RPC-M8-4FR-**-M12-4MR-PUR	4	T4052426004-00X	
					RPC-M8-4FR-**-M12-4MS-PUR	4	T4052425004-00X	
					RPC-M8-3FR-**-M12-3MR-PUR	3	T4052426003-00X	
					RPC-M8-3FR-**-M12-3MS-PUR	3	T4052425003-00X	
WIRES: 0.25mm ² (24AWG) WIRE COLOR:1-BROWN,3-BLUE, 4-BLACK OD: APROX. 4.5MM	TOLERANCE: 0m TO 1m: ±0.05m 1m TO 3m: ±0.1m >3m: ±1.5%	FIXED: -10°C~80°C FLXIBLE: -5°C~80°C	BLACK	PVC (UL)	RPC-M8-4FR-**-M12-4MR-PVC	4	T4052416004-00X	
					RPC-M8-4FR-**-M12-4MS-PVC	4	T4052415004-00X	
					RPC-M8-3FR-**-M12-3MR-PVC	3	T4052416003-00X	
					RPC-M8-3FR-**-M12-3MS-PVC	3	T4052415003-00X	
CABLE CHARACTERISTIC	LENGTH "L"	CABLE TEMP. RANGE	JACKET COLOR	JACKET MATERIAL	TYPE	7	POS. PART NUMBER	6

BLACK	PA66	END CAP	13
BLUE	TPU	M12 OVER-MOLDING	12
GOLD FLASH	COPPER ALLOY	MALE CONTACT	11
-	SUS	SPRING	10
NICKEL PLATED	COPPER ALLOY	M12, MALE NUT	9
BLACK	PA66	M12, MALE HSG, A CODE, 5PINS	8
-	-	CABLE	7
-	-	TE LABLE	6
BLUE	TPU	M8 RA OVERMOLDING	5
GRAY	SILICONE	O-RING	4
GOLD FLASH	COPPER ALLOY	M8 FEMALE CONTACT	3
NICKEL PLATED	COPPER ALLOY	M8 FEMALE NUT	2
BALCK COLOR	PA66	M8 FEMALE HOUSING	1
COMMENTS 备注	MATERIAL 材质	DESCRIPTION 描述	ITEM NO 序号

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4052416003-003](#)