


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	02MAR2016	N.P	X.X
	B	PER ECR-20-003177	08JUL2020	B.P	C.W



NOTES:

1. TECHNICAL DATA: SEE TABLE 1

2. RECOMMEND TORQUE 0.4Nm

3. TE LABLE AREA.

4. SEE TABLE 2, REFER TO LENGTH "L"
-**: CABLE LENGHT.-0.5:0.5m, -1.0:1.0m, -1.5:1.5m...

5. INSERT MARK FOR MATING.

6. SEE TABLE 2,REFER TO LENGTH "L"
CABLE LENGTH CODE:
STANDARD LENGTH:001...007
CUSTOMIZATION LENGTH:
>1.0M;XX0 OR XX5
EXAMPLE:3.5M:035;15.0M:150...
<1.0M;99X
EXAMPLE:0.4M:994;...0.9M:999

注意事项

1. 技术参数:见表1

2. 推荐扭矩0.4Nm;

3. TE 标签位置;

4. 参考表 2, 参照长度 "L"
-*: 线缆长度,-0.5:0.5M,-1.0:1.0M,-1.5:1.5M...


5. 产品对插标示;

6. 参照表2, 参考长度"L"
线缆长度编码:
标准长度:001...007
定制长度:>1.0M;XX0 或 XX5
例如:3.5M:035;15.0M:150...
<1.0M;99X
例如:0.4M:994;...0.9M:999

TABLE 1

TECHNICAL DATA	T40621X4003-00X	T40621X4004-00X
RATED VOLTAGE	60V	30V
RATED CURRENT	3A	
POLLETION DEGREE	3	
OVERVOLTAGE CATEGORY	II	
MATERIAL GROUP	II	
DEGREE OF PROTECTION	IP67	

-	-	TE LABLE	14
	STEEL	WAVE WASHER	13
	STEEL	SPRING	12
	BRASS	SHIELDING	11
-	-	CABLE	10
-	COPPER ALLOY	COUPLING NUT	9
	RUBBER	O-RING	8
BALCK COLOR	PA66	HOUSING	7
GOLD FLASH	COPPER ALLOY	CONTACT	6
	COPPER ALOY	SHIELDING	5
BLUE COLOR	POLYURETHANE	OVER-MOLDING	4
-	COPPER ALLOY	COUPLING NUT	3
BALCK COLOR	PA66	HOUSING	2
GOLD FLASH	COPPER ALLOY	CONTACT	1
COMMENTS	MATERIAL	DESCRIPITON	ITEM



WIRES: 0.25mm ² (24AWG)	STANDARD: -001:0.5M -002:1.0M -003:1.5M -004:3.0M -005:5.0M -006:7.0M -007:10.0M CUSTOMIZATION: -XX0:XX.0 M -XX5:XX.5 M -99X: 0.X M	FIXED: -25°C~80°C FLXIBLE: -10°C~80°C	GRAY	PUR (UL)	RPC-M8-4MS-**SH-M8-4FR-PUR	4	T4062124004-00X		
					RPC-M8-3MS-**SH-M8-3FR-PUR	3	T4062124003-00X		
		FIXED: -10°C~80°C FLXIBLE: -5°C~80°C	BLACK	PVC (UL)	RPC-M8-4MS-**SH-M8-4FR-PVC	4	T4062114004-00X		
					RPC-M8-3MS-**SH-M8-3FR-PVC	3	T4062114003-00X		
CABLE CHARACTERISTIC	LENGTH "L"	RECOMMEND OPERATION TEMPERATURE FOR CABLE	JACKET COLOR	JACKET MATERIAL	TYPE	POS.	PART NUMBER		
THIS DRAWING IS A CONTROLLED DOCUMENT.					DWN Nick Pan 23FEB2016 CHK Kobby Zhao 23FEB2016 APVD Xiang Xu 23FEB2016				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-106140	NAME M8 CABLE ASSEMBLY SHIELDED TYPE DOUBLE ENDED				
MATERIAL		FINISH		APPLICATION SPEC -	SIZE A2	CAGE CODE -	DRAWING NO C-T40621X400X00X		
CUSTOMER DRAWING					WEIGHT -	RESTRICTED TO -	REV B		
					SCALE 1:1	SHEET 1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4062124004-003](#)