






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	24FEB2016	N.P	X.X
	B	PER ECR-20-003177	08JUL2020	B.P	C.W




-	-	TE LABLE	14
	STEEL	WAVE WASHER	13
	STEEL	SPRING	12
	BRASS	SHIELDING	11
-	-	CABLE	10
-	COPPER ALLOY	COUPLING NUT	9
	RUBBER	O-RING	8
BALCK COLOR	PA66	HOUSING	7
GOLD FLASH	COPPER ALLOY	CONTACT	6
	COPPER ALOY	SHIELDING	5
BLUE COLOR	POLYURETHANE	OVER-MOLDING	4
-	COPPER ALLOY	COUPLING NUT	3
BALCK COLOR	PA66	HOUSING	2
GOLD FLASH	COPPER ALLOY	CONTACT	1
COMMENTS	MATERIAL	DESCRIPITON	ITEM

TABLE 1

TECHNICAL DATA	T40622X3003-00X	T40622X3004-00X
RATED VOLTAGE	60V	30V
RATED CURRENT	3A	
POLLETION DEGREE	3	
OVERVOLTAGE CATEGORY	II	
MATERIAL GROUP	II	
DEGREE OF PROTECTION	IP67	

VIEW A	T40622X3003-00X  PIN1 BROWN PIN2 WHITE PIN3 BLUE PIN4 BLACK	T40622X3004-00X  PIN1 BROWN PIN2 WHITE PIN3 BLUE PIN4 BLACK
VIEW B	 PIN1 BROWN PIN2 WHITE PIN3 BLUE PIN4 BLACK	 PIN1 BROWN PIN2 WHITE PIN3 BLUE PIN4 BLACK

WIRES: 0.25mm ² (24AWG)	STANDARD: -001:0.5M -002:1.0M -003:1.5M -004:3.0M -005:5.0M -006:7.0M -007:10.0M CUSTOMIZATION: -XX0:XX.0 M -XX5:XX.5 M -99X: 0.X M	FIXED: -25°C~80°C FLXIBLE: -10°C~80°C	GRAY	PUR (UL)	RPC-M8-4MR-**SH-M8-4FS-PUR [△]	4	T4062223004-00X [△]
					RPC-M8-3MR-**SH-M8-3FS-PUR [△]	3	T4062223003-00X [△]
		FIXED: -10°C~80°C FLXIBLE: -5°C~80°C	BLACK	PVC (UL)	RPC-M8-4MR-**SH-M8-4FS-PVC [△]	4	T4062213004-00X [△]
					RPC-M8-3MR-**SH-M8-3FS-PVC [△]	3	T4062213003-00X [△]
CABLE CHARACTERISTIC	LENGTH "L"	RECOMMEND OPERATION TEMPERATURE FOR CABLE	JACKET COLOR	JACKET MATERIAL	TYPE	POS.	PART NUMBER
		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Nick Pan CHK Kobby Zhao APVD Xiang Xu	24FEB2016 24FEB2016 24FEB2016	TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME M8 CABLE ASSEMBLY SHIELDED TYPE DOUBLE ENDED			
		0 PLC ± 1 PLC ±0.50 2 PLC ±0.35 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 108-106140			
		MATERIAL TBD		APPLICATION SPEC -		SIZE A2	
		FINISH -		WEIGHT -		CAGE CODE -	
				DRAWING NO T40622X300X00X		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 1:1		SHEET 1 OF 1	
				REV B			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4062223003-007](#)