




NOTES:

1. TECHNICAL DATA: SEE TABLE 1

2. RECOMMEND TORQUE 0.4Nm

3. TE LABEL AREA.

4. SEE TABLE 2, REFER TO LENGTH "L"

-*: CABLE LENGHT.-0.5:0.5m, -1.0:1.0m, -1.5:1.5m...

5. SEE TABLE 2,REFER TO LENGTH "L"

CABLE LENGTH CODE:

STANDARD LENGTH:001...007

CUSTOMIZATION LENGTH:

>1.0M;XX0 OR XX5

EXAMPLE:3.5M:035;15.0M:150...

<1.0M;99X

EXAMPLE:0.4M:994;...0.9M:999

注意事项

1. 技术参数：见表1

2. 推荐扭矩0.4Nm；

3. TE 标签位置；

4. 参考表 2， 参照长度 "L"

-*，*：线缆长度，-0.5:0.5M，-1.0:1.0M，-1.5:1.5M...

5. 参照表2，参考长度"L"

线缆长度编码：

标准长度：001...007

定制长度：>1.0M;XX0 或 XX5

例如：3.5M:035;15.0M:150...

<1.0M;99X

例如：0.4M:994;...0.9M:999




TABLE 1

TECHNICAL DATA	T40622X4003-00X	T40622X4004-00X
RATED VOLTAGE	60V	30V
RATED CURRENT	3A	
POLLETION DEGREE	3	
OVERVOLTAGE CATEGORY	II	
MATERIAL GROUP	II	
DEGREE OF PROTECTION	IP67	

-	-	TE LABEL	14
	STEEL	WAVE WASHER	13
	STEEL	SPRING	12
	BRASS	SHIELDING	11
-	-	CABLE	10
-	COPPER ALLOY	COUPLING NUT	9
	RUBBER	O-RING	8
BALCK COLOR	PA66	HOUSING	7
GOLD FLASH	COPPER ALLOY	CONTACT	6
	COPPER ALOY	SHIELDING	5
BLUE COLOR	POLYURETHANE	OVER-MOLDING	4
-	COPPER ALLOY	COUPLING NUT	3
BALCK COLOR	PA66	HOUSING	2
GOLD FLASH	COPPER ALLOY	CONTACT	1
COMMENTS	MATERIAL	DESCRIPITON	ITEM

WIRES: 0.25mm²
(24AWG)

STANDARD:
-001:0.5M
-002:1.0M
-003:1.5M
-004:3.0M
-005:5.0M
-006:7.0M
-007:10.0M
CUSTOMIZATION:
-XX0:XX.0 M
-XX5:XX.5 M
-99X: 0.X M

FIXED:
-25°C~80°C
FLXIBLE:
-10°C~80°C

FIXED:
-10°C~80°C
FLXIBLE:
-5°C~80°C

GRAY

BLACK

PUR
(UL)

PVC
(UL)

CABLE CHARACTERISTIC

LENGTH "L"

RECOMMEND OPERATION TEMPERATURE FOR CABLE

JACKET COLOR

JACKET MATERIAL

TYPE

POS.

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.50
2 PLC ±0.35
3 PLC ±
4 PLC ±
ANGLES ±
FINISH -

MATERIAL
TBD

DWN Nick Pan 24FEB2016

CHK Kobby Zhao 24FEB2016

APVD Xiang Xu 24FEB2016

PRODUCT SPEC
108-106140

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

M8 CABLE ASSEMBLY SHIELDED TYPE
DOUBLE ENDED

NAME

SIZE A2

CAGE CODE

DRAWING NO
C-T40622X400X00X

RESTRICTED TO

SCALE 1:1

SHEET 1 OF 1

REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4062214003-003](#)